

YAL1CT516, Compression Terminal

By Burndy
Catalog # [YAL1CT516](#)

Copper HYLUG™ , Single Hole w/ Inspection Window, #1 AWG,
5/16" Stud,11 index,Green, Short Barrel,Electro- Tin Plated



Application

Wire Termination

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance Status	CM
Certification - cULus	No
Industry Standard(s)	UL 486A-486B
UL Listed	Yes
Certification - CSA Approved	Yes

Conductor

Conductor - Copper DLO Size Range	N/A
Conductor Size	1 AWG
Conductor - Material	COPPER
Conductor Type	CODE
Conductor - Copper Str Size Range	1 AWG
Conductor - Copper Str Size	1 AWG

Configuration

Physical Attribute - Number of Holes	1
Connector Type	STANDARD BARREL

Current

Voltage Rating	35 kV
Voltage - Maximum	35000

Dimensions

Dimension - Pad Width inch	0.68 in
Dimension - Bolt Hole Size inch	0.33 in
Package Height	0.000 in
Dimension - Hole Size fraction	5/16
Dimension - Bolt Size fraction	5/16

Physical Attribute - Tongue Angle	Straight
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall mm	49 mm
Dimension - B Length inch	0.88 in
Dimension - Outside Diameter inch	0.46 in
Dimension - D inch	0.70 in
Dimension - N inch	0.34 in
Dimension - Hole Size mm	10 mm
Dimension - Bolt Size inch	0.3125
Dimension - Hole Size inch	0.38
Dimension - Length Overall inch	1.94 in
Dimension - Stud Size inch	5/16
Dimension - Stud Size fraction	5/16

General

Feature - Barrel Type	Standard
Feature - Barrel Style	Chamfered
Plated	Y
Color Code	Green
Trade Name	HYLUG™
Physical Attribute - Tongue Type	Standard
Die Index	11
UPC	781810416907
Type	Standard Barrel, Tin Plated
Material	COPPER
Plating Type	Tin - Electro Plated
Finish Type	Tin-Plated
UPC 14 Digit GTIN	00781810416907

Logistics

Carton Quantity	10
-----------------	----

Product Assets

[Catalog \[English\]](#)