



YAL26T12, Cu Compression, 1-Hole, 1/2" Stud, Standard Barrel, 2/0 AWG

By Burndy
Catalog # [YAL26T12](#)



Copper HYLUG™, Single Hole w/ Inspection Window, 2/0 AWG, 1/2" Stud, 13 index, Black, Short Barrel, Electro- Tin Plated

Application

Wire Termination

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance Status	CM
Certification - cULus	No
EU RoHS Indicator	Contact Manufacturer
Industry Standard(s)	UL 486A-486B
UL Listed	Yes
Certification - CSA Approved	Yes

Conductor

Conductor - Copper DLO Size Range	N/A
Conductor Size	2/0 AWG
Conductor - Material	COPPER
Conductor Type	CODE
Conductor - Copper Str Size Range	2/0 AWG
Conductor - Copper Str Size	2/0 AWG

Configuration

Physical Attribute - Number of Holes	1
Connector Type	STANDARD BARREL

Current

Voltage Rating	35 kV
Voltage - Maximum	35000

Dimensions

Dimension - Pad Width inch	0.83 in
Dimension - Bolt Hole Size inch	0.52 in
Package Height	0.000 in
Dimension - Hole Size fraction	1/2
Dimension - Bolt Size fraction	1/2

Physical Attribute - Tongue Angle	Straight
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall mm	62 mm
Dimension - B Length inch	0.94 in
Dimension - Outside Diameter inch	0.56 in
Dimension - D inch	1.06 in
Dimension - N inch	0.52 in
Dimension - Hole Size mm	13.5 mm
Dimension - Bolt Size inch	0.5
Dimension - Hole Size inch	0.53
Dimension - Length Overall inch	2.44 in
Dimension - Stud Size inch	1/2
Dimension - Stud Size fraction	1/2

General

Feature - Barrel Type	Standard
Feature - Barrel Style	Chamfered
Plated	Y
Color Code	Black
Trade Name	HYLUG™
Physical Attribute - Tongue Type	Standard
Die Index	13
UPC	781810416983
Type	Standard Barrel, Tin Plated
Construction Material - Main Material	Copper
Plating Type	COPPER
Finish Type	Tin - Electro Plated
UPC 14 Digit GTIN	Electro Tin plated
	00781810416983

Logistics

Carton Quantity	10
-----------------	----

Product Assets

[Catalog \[English\]](#)



A Hubbell brand