



BURNDY

[YAL2CT12, Compression Terminal](#)

By Burndy

Catalog # [YAL2CT12](#)

Copper HYLUG™, Single Hole w/ Inspection Window, 2 AWG, 1/2" Stud, 10 index, Brown, Short Barrel, Electro- Tin Plated



Application

Wire Termination

Specifications

Certification - ETL

No

Certification - UL Recognized

No

Standards - RoHS Compliance Status

CM

Certification - cULus

No
Industry Standard(s)
UL 486A-486B
UL Listed
Yes
Certification - CSA Approved
Yes

Conductor

Conductor - Copper DLO Size Range
N/A
Conductor Size
2 AWG
Conductor - Material
COPPER
Conductor Type
CODE
Conductor - Copper Str Size Range
2 AWG
Conductor - Copper Str Size
2 AWG

Configuration

Physical Attribute - Number of Holes
1
Connector Type
STANDARD BARREL

Current

Voltage Rating
35 kV
Voltage - Maximum
35000

Dimensions

Dimension - Pad Width inch
0.73 in
Dimension - Bolt Hole Size inch
0.52 in
Package Height
0.000 in
Dimension - Hole Size fraction
1/2
Dimension - Bolt Size fraction
1/2
Physical Attribute - Tongue Angle
Straight
Package Weight
0.000 lb.
Package Length
0.000 in
Package Width
0.000 in
Dimension - L Length Overall mm
59 mm
Dimension - B Length inch
0.88 in
Dimension - Outside Diameter inch
0.42 in
Dimension - D inch
1.08 in
Dimension - N inch
0.56 in
Dimension - Hole Size mm
13.5 mm
Dimension - Bolt Size inch
0.5
Dimension - Hole Size inch
0.53
Dimension - Length Overall inch
2.32 in
Dimension - Stud Size inch
1/2
Dimension - Stud Size fraction
1/2

General

Feature - Barrel Type
Standard
Feature - Barrel Style
Chamfered
Plated
Y
Color Code
Brown
Trade Name
HYLUG™
Physical Attribute - Tongue Type
Standard
Die Index
10
UPC
781810417157
Type
Standard Barrel, Tin Plated
Material
COPPER
Plating Type
Tin - Electro Plated
Finish Type
Tin-Plated
UPC 14 Digit GTIN
00781810417157

Logistics

Carton Quantity
25

Product Assets

[Catalog \[English\]](#)



A Hubbell brand
© 2026 Hubbell Incorporated. All rights reserved
BRDY_CA-YAL2CT12-SPEC-EN | REV 5/2026