

YAL30T916B, Compression Terminal

By Burndy

Catalog # [YAL30T916B](#)

One Hole Cu Compression Terminal with belled end, 300 Kcmil , 9/16" stud, Tin Plated.



Application

Wire Termination

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance Status	CM
Certification - cULus	No
Industry Standard(s)	UL 486A-486B
UL Listed	Yes
Certification - CSA Approved	Yes

Conductor

Conductor - Copper DLO Size Range	N/A
Conductor Size	300 KCMIL
Conductor - Material	COPPER
Conductor Type	CODE
Conductor - Copper Str Size Range	300 kcmil
Conductor - Copper Str Size	300 KCMIL

Configuration

Physical Attribute - Number of Holes	1
Connector Type	STANDARD BARREL

Current

Voltage Rating	35 kV
Voltage - Maximum	35000

Dimensions

Dimension - Pad Width inch	1.20 in
Package Height	0.000 in
Dimension - Hole Size fraction	1/2
Dimension - Bolt Size fraction	1/2
Physical Attribute - Tongue Angle	Straight
Dimension - B Length fraction	1 in
Package Weight	0.000 lb.
Package Length	0.000 in

Package Width	0.000 in
Dimension - Z inch	0.55 in
Dimension - L Length Overall mm	64 mm
Dimension - B Length inch	0.97 in
Dimension - Outside Diameter inch	0.81 in
Dimension - D inch	1.08 in
Dimension - N inch	0.53 in
Dimension - Inside Diameter inch	0.65 in
Dimension - Hole Size mm	14 mm
Dimension - Bolt Size inch	0.5
Dimension - Hole Size inch	0.56
Dimension - Length Overall inch	2.52 in
Dimension - Stud Size fraction	1/2

General

Feature - Barrel Type	Standard
Feature - Barrel Style	Belled
Plated	Y
Color Code	White
Trade Name	HYLUG™
Die Index	17
UPC	781810417232
Type	Standard Barrel, Tin Plated
Material	COPPER
Plating Type	Tin - Electro Plated
Finish Type	Tin-Plated
UPC 12 Digit	781810417232
UPC 14 Digit GTIN	00781810417232

Logistics

Pallet Quantity	13920
Carton Quantity	30

Operational

Temperature Rating	194
--------------------	-----

Product Assets

[Catalog \[English\]](#)