



YAL32T12, Compression Terminal

By Burndy
Catalog # [YAL32T12](#)

Copper HYLUG™, Single Hole w/ Inspection Window,400 kcmil,
1/2" Stud,19 index,Blue, Short Barrel,Electro- Tin Plated

Application

Wire Termination

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance Status	CM
Certification - cULus	No
Industry Standard(s)	UL 486A-486B
UL Listed	Yes
Certification - CSA Approved	Yes

Conductor

Conductor - Copper DLO Size Range	N/A
Conductor Size	400 KCMIL
Conductor - Material	COPPER
Conductor Type	CODE
Conductor - Copper Str Size Range	400 kcmil
Conductor - Copper Str Size	400 KCMIL

Configuration

Physical Attribute - Number of Holes	1
Connector Type	STANDARD BARREL

Current

Voltage Rating	35 kV
Voltage - Maximum	35000

Dimensions

Dimension - Pad Width inch	1.40 in
Dimension - Bolt Hole Size inch	0.52 in
Package Height	0.000 in
Dimension - Bolt Size fraction	1/2
Physical Attribute - Tongue Angle	Straight

Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - Z inch	0.55 in
Dimension - L Length Overall mm	74 mm
Dimension - B Length inch	1.19 in
Dimension - Outside Diameter inch	0.95 in
Dimension - D inch	1.08 in
Dimension - N inch	0.53 in
Dimension - Hole Size mm	13 mm
Dimension - Bolt Size inch	0.5
Dimension - Length Overall inch	2.93 in
Dimension - Stud Size inch	1/2

General

Feature - Barrel Type	Standard
Feature - Barrel Style	Chamfered
Plated	Y
Color Code	Blue
Trade Name	HYLUG™
Physical Attribute - Tongue Type	Standard
Die Index	19
UPC	781810417317
Type	Standard Barrel, Tin Plated
Material	COPPER
Plating Type	Tin - Electro Plated
Finish Type	Tin-Plated
UPC 14 Digit GTIN	00781810417317

Logistics

Pallet Quantity	9600
Carton Quantity	10

Product Assets

[Catalog \[English\]](#)