



YAS1R2N, Aluminum - Compression Stacking Terminal (HYLUG Terminal)

By Burndy
Catalog # [YAS1R2N](#)

Aluminum tubing stacking terminal-Straight lug, #2-#1 AWG
Al,Cu, #2 AWG ACSR, .56 IN Stud, Red, .65 IN H



Features

- Aluminum tubing stacking terminal-Straight lug
- #2-#1 AWG Al,Cu, #2 AWG ACSR

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance	CM
Status	
Certification - cULus	No
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - AL Str Size	2 AWG 1 AWG
Conductor - AL Str Size Range	2 AWG-1 AWG
Conductor - ACSR Str Size	2 (6/1) Sparrow AWG
Conductor - Copper Str Size Range	2 AWG-1 AWG
Conductor - Copper Str Size	2 AWG 1 AWG
Conductor - ACSR Str Size Range	2 (6/1) Sparrow AWG

Configuration

Physical Attribute - Number of Crimps Required	1
Physical Attribute - Number of Holes	2
Connector Type	Terminal

Dimensions

Dimension - Pad Width inch	0.90 in
Package Height	0.000 in
Physical Attribute - Tongue Angle	Straight

Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - Z inch	1.05 in
Dimension - L Length Overall mm	123 mm
Dimension - B Length inch	0.96 in
Dimension - Outside Diameter inch	0.65 in
Dimension - D inch	3.43 in
Dimension - N inch	0.63 in
Dimension - Hole Size inch	0.56 in
Dimension - Length Overall inch	4.85 in
Dimension - Strip Length inch	1-3/32 in

General

Feature - Barrel Style	Chamfered
Plated	N
Color Code	Red
Trade Name	HYLUG™
Die Index	- BG 243 - K-5/8-1 - CSA22
UPC	781810048900
Material	Aluminum Alloy
Plating Type	Unplated
UPC 12 Digit	781810048900
UPC 14 Digit GTIN	00781810048900

Logistics

Minimum Pack Quantity	20
Pallet Quantity	9280
Carton Quantity	20

Product Assets

[Catalog \[English\]](#)