



YAS1R2NTN, Aluminum Stacking Terminal, Straight

By Burndy
Catalog # [YAS1R2NTN](#)

Aluminum tubing stacking terminal-Straight lug, #2-#1 AWG
Al,Cu, #2 AWG ACSR, .56 IN Stud, Red, .65 IN H, Tin plated

Features

- Aluminum tubing stacking terminal-Straight lug
- #2-#1 AWG Al,Cu, #2 AWG ACSR
- Tin plated

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance	CM
Status	
Certification - cULus	No
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - AL Str Size	2 AWG 1 AWG
Conductor - AL Str Size Range	2 AWG-1 AWG
Conductor - ACSR Str Size	2 (6/1) Sparrow AWG
Conductor - Copper Str Size Range	2 AWG-1 AWG
Conductor - Copper Str Size	2 AWG 1 AWG
Conductor - ACSR Str Size Range	2 (6/1) Sparrow AWG

Configuration

Physical Attribute - Number of Holes	2
Connector Type	Terminal

Dimensions

Dimension - Pad Width inch	0.90 in
Physical Attribute - Tongue Angle	Straight



Dimension - Z inch	1.05 in
Dimension - L Length Overall mm	123 mm
Dimension - B Length inch	0.96 in
Dimension - Outside Diameter inch	0.65 in
Dimension - D inch	3.43 in
Dimension - N inch	0.63 in
Dimension - Hole Size inch	0.56 in
Dimension - Length Overall inch	4.85 in
Dimension - Strip Length inch	1-3/32 in

General

Feature - Barrel Style Plated	Chamfered Y
Color Code	Red
Trade Name	HYLUG™
Die Index	- BG 243 - K-5/8-1 - CSA22
UPC	781810263211
Material	Aluminum Alloy
Plating Type	Tin - Electro Plated
UPC 12 Digit	781810263211
UPC 14 Digit GTIN	00781810263211

Logistics

Minimum Pack Quantity	1
Pallet Quantity	9280
Carton Quantity	20

Product Assets

[Catalog \[English\]](#)