



YAS1RN, Aluminum Stacking Terminal, Straight

By Burndy
Catalog # [YAS1RN](#)

Aluminum Stacking Terminal- Straight Lug, #2-#1 AWG Al,Cu, #2 AWG ACSR, 1 Hole, Red



Features

- Aluminum Stacking Terminal - Straight
- #2-#1 AWG AL, Cu
- #2 AWG ACSR
- 1-Hole, Color Code Red

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance	CM
Status	
Certification - cULus	No
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - AL Str Size	2 AWG 1 AWG
Conductor - AL Str Size Range	2 AWG-1 AWG
Conductor - ACSR Str Size	2 (6/1) Sparrow AWG
Conductor - Copper Str Size Range	2 AWG-1 AWG
Conductor - Copper Str Size	2 AWG 1 AWG
Conductor - ACSR Str Size Range	2 (6/1) Sparrow AWG

Dimensions

Dimension - Pad Width inch	0.92 in
Dimension - Z inch	1.10 in
Dimension - P inch	1.29 in
Dimension - L Length Overall mm	77 mm

Dimension - B Length inch	0.96 in
Dimension - Outside Diameter inch	0.65 in
Dimension - N inch	0.63 in
Dimension - Inside Diameter inch	0.35 in
Dimension - Hole Size inch	0.56 in
Dimension - Length Overall inch	3.05 in
Dimension - Strip Length inch	1-3/32 in

General

Feature - Barrel Style	Chamfered
Plated	N
Color Code	Red
Trade Name	HYLUG™
Die Index	- BG 243 - K-5/8-1 - CSA22
UPC	781810093924
Material	Aluminum
Plating Type	Unplated
UPC 12 Digit	781810093924
UPC 14 Digit GTIN	00781810093924

Logistics

Minimum Pack Quantity	20
Pallet Quantity	19200
Carton Quantity	20

Product Assets

[Catalog \[English\]](#)