



YAS25R2NTN, Aluminum Stacking Terminal, Straight

By Burndy
Catalog # [YAS25R2NTN](#)

Aluminum tubing stacking terminal-Straight lug, 1/0 AWG
Al,Cu,ACSR, .56 IN Stud, Yellow, .65 IN H, Tin plated

Features

- Aluminum tubing stacking terminal-Straight lug
- 1/0 AWG Al,Cu,ACSR
- Tin plated

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance	CM
Status	
Certification - cULus	No
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - AL Str Size	1/0 AWG
Conductor - AL Str Size Range	1/0 AWG
Conductor - ACSR Str Size	1/0 (6/1) Raven AWG
Conductor - Copper Str Size	1/0 AWG
Range	
Conductor - Copper Str Size	1/0 AWG
Conductor - ACSR Str Size	1/0 (6/1) Raven AWG
Range	

Dimensions

Dimension - Pad Width inch	0.90 in
Dimension - Z inch	1.05 in
Dimension - P inch	1.29 in
Dimension - L Length Overall mm	77 mm
Dimension - B Length inch	0.96 in



Dimension - Outside Diameter inch	0.65 in
Dimension - N inch	0.63 in
Dimension - Inside Diameter inch	0.42 in
Dimension - Hole Size inch	0.56 in
Dimension - Length Overall inch	4.85 in
Dimension - Strip Length inch	1-3/32 in

General

Feature - Barrel Style	Chamfered
Plated	Y
Color Code	Yellow
Trade Name	HYLUG™
Die Index	- BG 243 - K-5/8-1 - CSA22
UPC	781810246542
Material	Aluminum
Plating Type	Tin - Electro Plated
UPC 12 Digit	781810246542
UPC 14 Digit GTIN	00781810246542

Logistics

Minimum Pack Quantity	1
Pallet Quantity	9280
Carton Quantity	20

Product Assets

[Catalog \[English\]](#)