



YAS26R2NTN, Aluminum Stacking Terminal, Straight

By Burndy
Catalog # [YAS26R2NTN](#)

Aluminum Stacking Terminal - Straight lug, 2/0 AWG Al, Cu 2/0 AWG ACSR, Gray, Tin Plating



Features

- Aluminum Stacking Terminal - Straight lug
- 2/0 AWG Al, Cu 2/0 AWG ACSR
- Tin Plating

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance Status	CM
Certification - cULus	No
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - AL Str Size	2/0 AWG
Conductor - AL Str Size Range	2/0 AWG
Conductor - ACSR Str Size	2/0 (6/1) Quail AWG
Conductor - Copper Str Size Range	2/0 AWG
Conductor - Copper Str Size	2/0 AWG
Conductor - ACSR Str Size	2/0 (6/1) Quail AWG
Conductor - Copper Str Size Range	

Configuration

Physical Attribute - Number of Holes	2
Connector Type	Terminal

Dimensions

Dimension - Pad Width inch	1.24 in
Physical Attribute - Tongue Angle	Straight
Dimension - Z inch	1.38 in

Dimension - L Length Overall mm	148 mm
Dimension - B Length inch	1.47 in
Dimension - Outside Diameter inch	0.91 in
Dimension - D inch	3.8 in
Dimension - N inch	0.63 in
Dimension - Inside Diameter inch	0.47 in
Dimension - Hole Size inch	0.56 in
Dimension - Length Overall inch	5.83 in
Dimension - Strip Length inch	1-19/32 in

General

Feature - Barrel Style	Chamfered
Plated	Y
Color Code	Gray
Trade Name	HYLUG™
Die Index	249 840 - CSA24
UPC	781810144619
Material	Aluminum Alloy
Plating Type	Tin - Electro Plated
UPC 12 Digit	781810144619
UPC 14 Digit GTIN	00781810144619

Logistics

Minimum Pack Quantity	20
Pallet Quantity	5920
Carton Quantity	20

Product Assets

[Catalog \[English\]](#)