



YAS27R2N, Aluminum - Compression Stacking Terminal (HYLUG Terminal)

By Burndy
Catalog # [YAS27R2N](#)

Straight Stacking Lug, Al Tubing, 2-NEMA Holes, 3/0 AWG Cu/Al,ACSR, Black, 0.56" Hole Dia.

Features

- Straight Stacking Lug
- Al Tubing
- 2-NEMA Holes
- 3/0 AWG Cu/Al,ACSR

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance	CM
Status	
Certification - cULus	No
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - AL Str Size	3/0 AWG
Conductor - AL Str Size Range	3/0 AWG
Conductor - ACSR Str Size	3/0 (6/1) Pigeon AWG
Conductor - Copper Str Size	3/0 AWG
Range	
Conductor - Copper Str Size	3/0 AWG
Conductor - ACSR Str Size	3/0 (6/1) Pigeon AWG
Range	

Configuration

Physical Attribute - Number of Crimps Required	1
Physical Attribute - Number of Holes	2
Connector Type	Terminal

Dimensions

Dimension - Pad Width inch	1.24 in
----------------------------	---------



Physical Attribute - Tongue Angle	Straight
Dimension - Z inch	1.38 in
Dimension - L Length Overall mm	148 mm
Dimension - B Length inch	1.47 in
Dimension - D inch	3.76 in
Dimension - N inch	0.63 in
Dimension - Hole Size inch	0.56 in
Dimension - Length Overall inch	5.83 in
Dimension - Strip Length inch	1-19/32 in

General

Feature - Barrel Style	Tapered
Plated	N
Color Code	Black
Trade Name	HYLUG™
Die Index	• 249 • 840 • CSA24
UPC	781810051696
Material	Aluminum
Plating Type	Unplated
UPC 12 Digit	781810051696
UPC 14 Digit GTIN	00781810051696

Logistics

Minimum Pack Quantity	1
Pallet Quantity	5920
Carton Quantity	20

Product Assets

[Catalog \[English\]](#)