



YAS27RN, Aluminum - Compression Stacking Terminal (HYLUG Terminal)

By Burndy
Catalog # [YAS27RN](#)

Al Stackable compression Terminal- Straight Lug, 3/0 Al-Cu, 3/0 ACSR, 1 Hole, Black



Features

- Al Stackable compression Terminal- Straight Lug
- 3/0 Al-Cu, 3/0 ACSR
- 1 Hole

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance Status	CM
Certification - cULus	No
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - AL Str Size	3/0 AWG
Conductor - AL Str Size Range	3/0 AWG
Conductor - ACSR Str Size	3/0 (6/1) Pigeon AWG
Conductor - Copper Str Size Range	3/0 AWG
Conductor - Copper Str Size	3/0 AWG
Conductor - ACSR Str Size	3/0 (6/1) Pigeon AWG
Conductor - Copper Str Size Range	

Configuration

Physical Attribute - Number of Crimps Required	1
Physical Attribute - Number of Holes	1
Connector Type	Terminal

Dimensions

Dimension - Pad Width inch	1.24 in
----------------------------	---------

Physical Attribute - Tongue Angle	Straight
Dimension - L Length Overall mm	103 mm
Dimension - B Length inch	1.47 in
Dimension - Outside Diameter inch	0.91 in
Dimension - D inch	2.01 in
Dimension - N inch	0.63 in
Dimension - Hole Size inch	0.56 in
Dimension - Length Overall inch	4.07 in
Dimension - Strip Length inch	1-19/32 in

General

Feature - Barrel Style	Chamfered
Plated	N
Color Code	Black
Trade Name	HYLUG™
Die Index	• 249 • 840 • CSA24
UPC	781810093948
Material	Aluminum Alloy
Plating Type	Unplated
UPC 12 Digit	781810093948
UPC 14 Digit GTIN	00781810093948

Logistics

Minimum Pack Quantity	20
Pallet Quantity	9280
Carton Quantity	20

Product Assets

[Catalog \[English\]](#)