



YAS28R2N, Aluminum - Compression Stacking Terminal (HYLUG Terminal)

By Burndy
Catalog # [YAS28R2N](#)

Aluminum Stacking Terminal - Straight lug, 4/0 AWG Al, Cu 4/0 AWG ACSR, Pink



Features

- Aluminum Stacking Terminal - Straight lug
- 4/0 AWG Al, Cu 4/0 AWG ACSR

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance	CM
Status	
Certification - cULus	No
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - AL Str Size	4/0 AWG
Conductor - AL Str Size Range	4/0 AWG
Conductor - ACSR Str Size	4/0 (6/1) Penguin AWG
Conductor - Copper Str Size Range	4/0 AWG
Conductor - Copper Str Size	4/0 AWG
Conductor - ACSR Str Size Range	4/0 (6/1) Penguin AWG

Configuration

Physical Attribute - Number of Crimps Required	1
Physical Attribute - Number of Holes	2
Connector Type	Terminal

Dimensions

Dimension - Pad Width inch	1.24 in
Package Height	0.000 in
Physical Attribute - Tongue Angle	Straight
Package Weight	0.000 lb.

Package Length	0.000 in
Package Width	0.000 in
Dimension - Z inch	1.38 in
Dimension - L Length Overall mm	148 mm
Dimension - B Length inch	1.47 in
Dimension - Outside Diameter inch	0.91 in
Dimension - D inch	3.76 in
Dimension - N inch	0.63 in
Dimension - Hole Size inch	0.56 in
Dimension - Length Overall inch	5.83 in
Dimension - Strip Length inch	1-19/32 in

General

Feature - Barrel Style	Tapered
Plated	N
Color Code	Pink
Trade Name	HYLUG™
Die Index	249 840 - CSA24
UPC	781810050422
Material	Aluminum
Plating Type	Unplated
UPC 12 Digit	781810050422
UPC 14 Digit GTIN	00781810050422

Logistics

Minimum Pack Quantity	1
Pallet Quantity	5920
Carton Quantity	20

Product Assets

[Catalog \[English\]](#)