



YAS28RN, Aluminum - Compression Stacking Terminal (HYLUG Terminal)

By Burndy
Catalog # [YAS28RN](#)

Al Stackable compression Terminal- Straight Lug, 4/0 Al-Cu, 4/0 ACSR, 1 Hole, Pink



Features

- Al Stackable compression Terminal- Straight Lug
- 4/0 Al-Cu, 4/0 ACSR
- 1 Hole

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance	CM
Status	
Certification - cULus	No
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - AL Str Size	4/0 AWG
Conductor - AL Str Size Range	4/0 AWG
Conductor - ACSR Str Size	4/0 (6/1) Penguin AWG
Conductor - Copper Str Size	4/0 AWG
Range	
Conductor - Copper Str Size	4/0 AWG
Conductor - ACSR Str Size	4/0 (6/1) Penguin AWG
Range	

Configuration

Physical Attribute - Number of Crimps Required	1
Physical Attribute - Number of Holes	1
Connector Type	Terminal

Dimensions

Dimension - Pad Width inch	1.24 in
----------------------------	---------

Physical Attribute - Tongue Angle	Straight
Dimension - L Length Overall mm	103 mm
Dimension - B Length inch	1.47 in
Dimension - D inch	2.01 in
Dimension - N inch	0.63 in
Dimension - Hole Size inch	0.56 in
Dimension - Length Overall inch	4.07 in
Dimension - Strip Length inch	1-19/32 in

General

Feature - Barrel Style	Chamfered
Plated	N
Color Code	Pink
Trade Name	HYLUG™
Die Index	• 249 • 840 • CSA24
UPC	781810093962
Material	Aluminum Alloy
Plating Type	Unplated
UPC 12 Digit	781810093962
UPC 14 Digit GTIN	00781810093962

Logistics

Minimum Pack Quantity	1
Pallet Quantity	9280
Carton Quantity	20

Product Assets

[Catalog \[English\]](#)