



YAS30R2N, Aluminum - Compression Stacking Terminal (HYLUG Terminal)

By Burndy
Catalog # [YAS30R2N](#)

Aluminum Stacking terminal - Straight lug, 250, 300 Kcmil Al, 266 Kcmil Cu ACSR, Blue



Features

- Aluminum Stacking terminal - Straight lug
- 250, 300 kcmil Al, 266 kcmil Cu ACSR

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance Status	CM
Certification - cULus	No
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - AL Str Size	250 kcmil 266 kcmil 300 kcmil
Conductor - AL Str Size Range	250 kcmil-300 kcmil
Conductor - ACSR Str Size	266.8 (18/1) Waxwing kcmil
Conductor - Copper Str Size Range	250 kcmil-300 kcmil
Conductor - Copper Str Size	250 kcmil 300 kcmil
Conductor - ACSR Str Size Range	266.8 (18/1) Waxwing kcmil

Configuration

Physical Attribute - Number of Crimps Required	1
Physical Attribute - Number of Holes	2
Connector Type	Terminal

Dimensions

Dimension - Pad Width inch	1.22 in
----------------------------	---------

Physical Attribute - Tongue Angle	Straight
Dimension - Z inch	1.79 in
Dimension - L Length Overall mm	167 mm
Dimension - B Length inch	1.85 in
Dimension - Outside Diameter inch	1.24 in
Dimension - N inch	0.63 in
Dimension - Hole Size inch	0.56 in
Dimension - Length Overall inch	6.59 in
Dimension - Strip Length inch	2 in

General

Plated	N
Color Code	Blue
Trade Name	HYLUG™
Die Index	317 705 - CSA26 - K-1-1/8-1
UPC	781810052150
Material	Aluminum
Plating Type	Unplated
UPC 12 Digit	781810052150
UPC 14 Digit GTIN	00781810052150

Logistics

Minimum Pack Quantity	1
Pallet Quantity	2880
Carton Quantity	20

Product Assets

[Catalog \[English\]](#)