

YAS30R2NTN, Aluminum Stacking Terminal, Straight

By Burndy
Catalog # [YAS30R2NTN](#)

Aluminum Stacking terminal - Straight lug, 250, 300 Kcmil Al, 266 Kcmil Cu ACSR, Blue, Tin plated



Features

- Aluminum Stacking terminal - Straight lug
- 250, 300 kcmil Al, 266 Kcmil Cu ACSR
- Tin plated

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance	CM
Status	
Certification - cULus	No
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - AL Str Size	• 250 kcmil • 266 kcmil • 300 kcmil
Conductor - AL Str Size Range	250 kcmil-300 kcmil
Conductor - ACSR Str Size	266.8 (18/1) Waxwing kcmil
Conductor - Copper Str Size Range	250 kcmil-300 kcmil
Conductor - Copper Str Size	• 250 kcmil • 300 kcmil
Conductor - ACSR Str Size Range	266.8 (18/1) Waxwing kcmil

Configuration

Physical Attribute - Number of Holes	2
Connector Type	Terminal

Dimensions

Dimension - Pad Width inch	1.22 in
Physical Attribute - Tongue Angle	Straight
Dimension - Z inch	1.79 in

Dimension - P inch	2.43 in
Dimension - L Length Overall mm	167 mm
Dimension - B Length inch	1.85 in
Dimension - Outside Diameter inch	1.24 in
Dimension - D inch	4.17 in
Dimension - N inch	0.63 in
Dimension - Inside Diameter inch	0.67 in
Dimension - Hole Size inch	0.56 in
Dimension - Length Overall inch	6.59 in
Dimension - Strip Length inch	2 in

General

Feature - Barrel Style Plated	Chamfered Y
Color Code	Blue
Trade Name	HYLUG™
Die Index	• 317 • 705 • CSA26 • K-1-1/8-1
UPC	781810416648
Material	Aluminum
Plating Type	Tin - Electro Plated
UPC 12 Digit	781810416648
UPC 14 Digit GTIN	00781810416648

Logistics

Minimum Pack Quantity	1
Pallet Quantity	2880
Carton Quantity	20

Product Assets

[Catalog \[English\]](#)