



YAS321RN, Aluminum - Compression Stacking Terminal (HYLUG Terminal)

By Burndy
Catalog # [YAS321RN](#)

Al Stackable Terminal-Straight Lug, 350 Kcmil Al-Cu, 336 Kcmil ACSR, Green

Features

- Al Stackable Terminal-Straight Lug
- 350 kcmil Al-Cu, 336 kcmil ACSR

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance	CM
Status	
Certification - cULus	No
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - AL Str Size	350
Conductor - AL Str Size Range	350
Conductor - ACSR Str Size	336.0 (18/1)
Conductor - Copper Str Size	350
Range	
Conductor - Copper Str Size	350
Conductor - ACSR Str Size	336.0 (18/1)
Range	

Configuration

Physical Attribute - Number of Crimps Required	1
Physical Attribute - Number of Holes	1
Connector Type	Terminal

Dimensions

Dimension - Pad Width inch	1.24 in
Physical Attribute - Tongue Angle	Straight



Dimension - Z inch	1.79 in
Dimension - L Length Overall mm	124 mm
Dimension - B Length inch	1.85 in
Dimension - Outside Diameter inch	1.24 in
Dimension - D inch	2.42 in
Dimension - N inch	0.63 in
Dimension - Hole Size inch	0.56 in
Dimension - Length Overall inch	4.89 in
Dimension - Strip Length inch	2 in

General

Plated	N
Color Code	Green
Trade Name	HYLUG™
Die Index	317 705 - CSA26 - K-1-1/8-1
UPC	781810120965
Material	Aluminum Alloy
Plating Type	Unplated
UPC 12 Digit	781810120965
UPC 14 Digit GTIN	00781810120965

Logistics

Minimum Pack Quantity	1
Pallet Quantity	4800
Carton Quantity	20

Product Assets

[Catalog \[English\]](#)