



YAS33R2N, Aluminum - Compression Stacking Terminal (HYLUG Terminal)

By Burndy
Catalog # [YAS33R2N](#)

Straight Stacking Lug, Al Tubing, 2-NEMA Holes, 400 kcmil
Cu/Al, 397 kcmil ACSR, Green, 0.56" Hole Dia.

Features

- Straight Stacking Lug, Al Tubing
- 2-NEMA Holes
- 400 kcmil Cu/Al, 397 kcmil ACSR

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance	CM
Status	
Certification - cULus	No
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - AL Str Size	400 kcmil
Conductor - AL Str Size Range	400 kcmil
Conductor - ACSR Str Size	397.5 (18/1) Chickadee kcmil
Conductor - Copper Str Size	400 kcmil
Range	
Conductor - Copper Str Size	400 kcmil
Conductor - ACSR Str Size	397.5 (18/1) Chickadee kcmil
Range	

Configuration

Physical Attribute - Number of Crimps Required	1
Physical Attribute - Number of Holes	2
Connector Type	Terminal

Dimensions

Dimension - Pad Width inch	1.68 in
----------------------------	---------



Physical Attribute - Tongue Angle	Straight
Dimension - Z inch	1.82 in
Dimension - L Length Overall mm	182 mm
Dimension - B Length inch	2.3 in
Dimension - Outside Diameter inch	1.24 in
Dimension - N inch	0.63 in
Dimension - Hole Size inch	0.56 in
Dimension - Length Overall inch	7.18 in
Dimension - Strip Length inch	2 in

General

Plated	N
Color Code	Green
Trade Name	HYLUG™
Die Index	• 317 • 705
UPC	781810051795
Material	Aluminum
Plating Type	Unplated
UPC 12 Digit	781810051795
UPC 14 Digit GTIN	00781810051795

Logistics

Minimum Pack Quantity	1
Pallet Quantity	2880
Carton Quantity	20

Product Assets

[Catalog \[English\]](#)