



YAS33RN, Aluminum Stacking Terminal, Straight

By Burndy
Catalog # [YAS33RN](#)

Al Stackable Terminal-Straight Lug, 400 Kcmil Al-Cu, 397 Kcmil ACSR, Green

Features

- Al Stackable Terminal-Straight Lug
- 400 kcmil Al-Cu, 397 kcmil ACSR

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance	CM
Status	
Certification - cULus	No
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - AL Str Size	400 kcmil
Conductor - AL Str Size Range	400 kcmil
Conductor - ACSR Str Size	397.0 (18/1)
Conductor - Copper Str Size	400 kcmil
Conductor - Copper Str Size Range	
Conductor - Copper Str Size	400 kcmil
Conductor - ACSR Str Size	397.0 (18/1)
Conductor - ACSR Str Size Range	

Configuration

Physical Attribute - Number of Crimps Required	1
Physical Attribute - Number of Holes	1
Connector Type	Terminal

Dimensions

Dimension - Pad Width inch	1.68 in
Physical Attribute - Tongue Angle	Straight

Dimension - Z inch	1.82 in
Dimension - L Length Overall mm	138 mm
Dimension - B Length inch	2.3 in
Dimension - Outside Diameter inch	1.24 in
Dimension - D inch	2.45 in
Dimension - N inch	0.63 in
Dimension - Hole Size inch	0.56 in
Dimension - Length Overall inch	5.43 in
Dimension - Strip Length inch	2 in

General

Plated	N
Color Code	Green
Trade Name	HYLUG™
Die Index	• 317 • 705 • CSA26 • K-1-1/8-1
UPC	781810368534
Material	Aluminum Alloy
Plating Type	Unplated
UPC 12 Digit	781810368534
UPC 14 Digit GTIN	00781810368534

Logistics

Pallet Quantity	4800
Carton Quantity	20

Product Assets

[Catalog \[English\]](#)