



YAS361R2N, Aluminum - Compression Stacking Terminal (HYLUG Terminal)

By Burndy
Catalog # [YAS361R2N](#)

Straight Stacking Lug, Al Tubing, 2-NEMA Holes, 500 Al/Cu, 477
ACSR, Pink, 0.56" Hole Dia.

Features

- Straight Stacking Lug
- Al Tubing
- 2-NEMA Holes
- 500 Al/Cu, 477 ACSR

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance	CM
Status	
Certification - cULus	No
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - AL Str Size	500 kcmil
Conductor - AL Str Size Range	500 kcmil
Conductor - ACSR Str Size	477.0 (18/1) Pelican kcmil
Conductor - Copper Str Size	500 kcmil
Range	
Conductor - Copper Str Size	500 kcmil
Conductor - ACSR Str Size	477.0 (18/1) Pelican kcmil
Range	

Configuration

Physical Attribute - Number of Crimps Required	2
Physical Attribute - Number of Holes	2
Connector Type	Terminal

Dimensions

Dimension - Pad Width inch	1.68 in
----------------------------	---------



Physical Attribute - Tongue Angle	Straight
Dimension - Z inch	1.98 in
Dimension - L Length Overall mm	192 mm
Dimension - B Length inch	2.46 in
Dimension - Outside Diameter inch	1.5 in
Dimension - N inch	0.63 in
Dimension - Hole Size inch	0.56 in
Dimension - Length Overall inch	7.55 in
Dimension - Strip Length inch	2-19/32 in

General

Feature - Barrel Style	Chamfered
Plated	N
Color Code	Pink
Trade Name	HYLUG™
Die Index	• 608 • 722 • K-1-5/16 • CSA28
UPC	781810052006
Material	Aluminum Alloy
Plating Type	Unplated
UPC 12 Digit	781810052006
UPC 14 Digit GTIN	00781810052006

Logistics

Minimum Pack Quantity	5
Pallet Quantity	1800
Carton Quantity	20

Product Assets

[Catalog \[English\]](#)