



YAS39A2NTN, Aluminum - Compression
Stacking Terminal, Straight Lug, 700-750
kcmil Al, 2-Hole, 1/2" Stud, 1-3/4" Spacing,
Tin Plated

By Burndy
Catalog # [YAS39A2NTN](#)

Aluminum Stacking Terminal- Straight Lug, 700-750 Kcmil Al, Cu,
2 Hole, Yellow, Tin Plating

Features

- Aluminum Stacking Terminal- Straight Lug
- 700-750 kcmil Al, Cu
- 2 Hole
- Tin Plating

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance	CM
Status	
Certification - cULus	No
UL Listed	No
Certification - CSA Approved	No

Dimensions

Dimension - Pad Width inch	1.68 in
Package Height	0.000 in
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - Z inch	1.98 in
Dimension - B Length inch	2.46 in
Dimension - Outside Diameter inch	1.5 in
Dimension - N inch	0.63 in



Dimension - Hole Size inch	0.56 in
Dimension - Length Overall inch	7.63 in
Dimension - Strip Length inch	2-19/32 in

General

Plated	Y
Color Code	Yellow
Trade Name	HYLUG™
Die Index	• 608 • 722 • K-1-5/16 • CSA28
UPC	781810162149
Material	Aluminum Alloy
Plating Type	Tin - Electro Plated
UPC 12 Digit	781810162149
UPC 14 Digit GTIN	00781810162149

Logistics

Minimum Pack Quantity	1
Pallet Quantity	2400
Carton Quantity	10

Product Assets

[Catalog \[English\]](#)