



YAS6R2N, Aluminum - Compression Stacking Terminal (HYLUG Terminal)

By Burndy
Catalog # [YAS6R2N](#)

Straight Stacking Lug, Al Tubing, 2-NEMA Holes, #6 - #5 AWG
Cu/Al, #6 AWG ACSR, Blue, 0.56" Hole Dia.

Features

- Straight Stacking Lug
- Al Tubing
- 2-NEMA Holes
- #6 - #5 AWG Cu/Al, #6 AWG ACSR

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance	CM
Status	
Certification - cULus	No
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - AL Str Size	6 AWG
Conductor - AL Str Size Range	6 AWG
Conductor - ACSR Str Size	6 (6/1) Turkey AWG
Conductor - Copper Str Size	6 AWG-5 AWG
Conductor - Copper Str Size Range	• 6 AWG • 5 AWG
Conductor - ACSR Str Size Range	6 (6/1) Turkey AWG

Configuration

Physical Attribute - Number of Crimps Required	1
Physical Attribute - Number of Holes	2
Connector Type	Terminal

Dimensions

Dimension - Pad Width inch	0.90 in
Package Height	0.000 in
Physical Attribute - Tongue Angle	Straight



Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - Z inch	1.05 in
Dimension - L Length Overall mm	123 mm
Dimension - B Length inch	0.96 in
Dimension - Outside Diameter inch	0.65 in
Dimension - D inch	3.43 in
Dimension - N inch	0.63 in
Dimension - Hole Size inch	0.56 in
Dimension - Length Overall inch	4.85 in
Dimension - Strip Length inch	1-3/32 in

General

Feature - Barrel Style	Chamfered
Plated	N
Color Code	Blue
Trade Name	HYLUG™
Die Index	• BG • K-5/8-1 • 243
UPC	781810048481
Material	Aluminum Alloy
Plating Type	Unplated
UPC 12 Digit	781810048481
UPC 14 Digit GTIN	00781810048481

Logistics

Minimum Pack Quantity	1
Pallet Quantity	9280
Carton Quantity	20

Product Assets

[Catalog \[English\]](#)