

YASO25R2N, Aluminum - Compression Stacking Terminal (HYLUG Terminal)

By Burndy
Catalog # [YASO25R2N](#)

Aluminum tubing stacking terminal-Stacking lug, 1/0 AWG
Al,Cu,ACSR, .56 IN Stud, Yellow, 1.21 IN H

Features

- Aluminum tubing stacking terminal-Stacking lug
- 1/0 AWG Al,Cu,ACSR

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance	CM
Status	
Certification - cULus	No
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - AL Str Size	1/0 AWG
Conductor - AL Str Size Range	1/0 AWG
Conductor - ACSR Str Size	1/0 (6/1) Raven AWG
Conductor - Copper Str Size	1/0
Range	
Conductor - Copper Str Size	1/0
Conductor - ACSR Str Size	1/0 (6/1) Raven AWG
Range	

Configuration

Physical Attribute - Number of	1
Crimps Required	
Physical Attribute - Number of	2
Holes	
Connector Type	Terminal

Dimensions

Dimension - Pad Width inch	0.90 in
Physical Attribute - Tongue	Offset
Angle	



Dimension - Height inch	1.21 in
Dimension - Height fraction	1-1/5 in
Dimension - Z inch	0.64 in
Dimension - L Length Overall	123 mm
mm	
Dimension - B Length inch	0.96 in
Dimension - Outside Diameter	0.65 in
inch	
Dimension - D inch	3.02 in
Dimension - N inch	0.63 in
Dimension - Hole Size inch	0.56 in
Dimension - Length Overall	4.85 in
inch	
Dimension - Strip Length inch	1-3/32 in

General

Feature - Barrel Style	Chamfered
Plated	N
Color Code	Yellow
Trade Name	HYLUG™
Die Index	- BG - K-5/8-1 243
UPC	781810053621
Material	Aluminum Alloy
Plating Type	Unplated
UPC 12 Digit	781810053621
UPC 14 Digit GTIN	00781810053621

Logistics

Pallet Quantity	9280
Carton Quantity	20

Product Assets

[Catalog \[English\]](#)