



YASO27R2N, Aluminum - Compression Stacking Terminal (HYLUG Terminal)

By Burndy
Catalog # [YASO27R2N](#)

Aluminum Stacking Terminal - Satcking lug, 3/0 AWG Al, Cu 3/0
AWG ACSR, Black



Features

- Aluminum Stacking Terminal - Stacking lug
- 3/0 AWG Al, Cu 3/0 AWG ACSR

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance	CM
Status	
Certification - cULus	No
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - AL Str Size	3/0 AWG
Conductor - AL Str Size Range	3/0 AWG
Conductor - ACSR Str Size	3/0 (6/1) Pigeon AWG
Conductor - Copper Str Size	3/0 AWG
Range	
Conductor - Copper Str Size	3/0 AWG
Conductor - ACSR Str Size	3/0 (6/1) Pigeon AWG
Range	

Configuration

Physical Attribute - Number of	1
Crimps Required	
Physical Attribute - Number of	2
Holes	
Connector Type	Terminal

Dimensions

Dimension - Pad Width inch	1.24 in
----------------------------	---------

Physical Attribute - Tongue	Offset
Angle	
Dimension - Z inch	0.72 in
Dimension - L Length Overall	148 mm
mm	
Dimension - B Length inch	1.47 in
Dimension - D inch	3.10 in
Dimension - N inch	0.63 in
Dimension - Hole Size inch	0.56 in
Dimension - Length Overall	5.83 in
inch	
Dimension - Strip Length inch	1-19/32 in

General

Feature - Barrel Style	Tapered
Plated	N
Color Code	Black
Trade Name	HYLUG™
Die Index	249 840 - CSA24
UPC	781810051733
Material	Aluminum
Plating Type	Unplated
UPC 12 Digit	781810051733
UPC 14 Digit GTIN	00781810051733

Logistics

Minimum Pack Quantity	1
Pallet Quantity	5920
Carton Quantity	20

Product Assets

[Catalog \[English\]](#)