



YAV10L36NK, Uninsulated Ring Terminal
For 12 - 10 AWG (Nickel Plated)

By Burndy
Catalog # [YAV10L36NK](#)



Uninsulated Ring Terminal For 12 - 10 AWG (Nickel Plated)

Features

- Nickel plated for high temperature applications up to 650°F continuous service and 750°F intermittent service
- Manufactured from seamless pure electrolytic copper tubing to provide maximum conductivity, low resistance, and excellent ductility for crimping
- Double thick tongue provides a structurally strong terminal tongue
- Produced from tubular copper, extra copper material assures the ompression terminal will operate cooler than the conductors it connects
- Internally beveled barrel for easy cable entry, especially for flexible conductors
- Inspection hole provides easy visual check for proper conductor insertion

Specifications

Certification - cULus	No
Certification - UL Recognized	No
Certification - ETL	No
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	CM
Industry Standard(s)	UL467
Certification - CSA Approved	No
UL Listed	No

Conductor

Conductor - Copper Solid Size	• 12 AWG • 11 AWG • 10 AWG
Conductor - Copper Solid Size Range	12 AWG-10 AWG
Conductor Size	12 - 10 AWG
Conductor - Copper Str Size	• 12 AWG • 10 AWG
Conductor - Copper Str Size Range	12 AWG-10 AWG
Conductor Type	• CU C Str-Size

- CU C Str Aircraft-Size

Configuration

Physical Attribute - Number of Holes	1
Connector Type	Ring Terminal

Dimensions

Package Length	0.000 in
Package Width	0.000 in
Package Weight	0.000 lb.
Dimension - Z inch	0.23 in
Dimension - Pad Width inch	0.29 in
Package Height	0.000 in
Dimension - Bolt Size fraction	#8 - #10
Dimension - Stud Size inch	• #8 • #10
Dimension - Length Overall inch	0.86 in

General

Physical Attribute - Tongue Type	Ring
Trade Name	HYLUG™
Plated	Y
Feature - Barrel Type	Standard
Feature - Barrel Style	Chamfered
Type	Ring Tongue
UPC 12 Digit	781810086070
UPC 14 Digit GTIN	00781810086070
Material	Copper
Plating Type	Nickel
UPC	781810086070

Logistics

Minimum Pack Quantity	200
Carton Quantity	200

Product Assets

[Catalog \[English\]](#)