



YAV10T23F, Uninsulated Fork Terminal For 12 - 10 AWG

By Burndy

Catalog # [YAV10T23F](#)

Uninsulated Fork Terminal For 12 - 10 AWG



Features

- Manufactured from seamless pure electrolytic copper tubing to provide maximum conductivity, low resistance and excellent ductility for crimping
- Seamless tubular crimp barrel design - No seams to split resulting in a very high quality electrical connection, also can be used on solid conductor
- Double thick tongue structurally a very strong terminal tongue
- Produced from tubular copper, extra copper material assures the compression connector will operate cooler than the conductors it connects
- Internally bevelled barrel for easy cable entry, especially for flexible conductors
- Inspection hole provides easy visual check for proper conductor insertion
- Electro-tin plated for a long lasting durable corrosion resistance


Specifications

Certification - cULus	No
Certification - UL Recognized	No
Certification - ETL	No
Standards - Industry Standards Met	UL486
Standards - RoHS Compliance Status	CM
Industry Standard(s)	UL467
Certification - CSA Approved	Yes
UL Listed	Yes

Conductor

Conductor - Copper Str Aircraft Size	• AN 12 • AN 10
Conductor - Copper Str Aircraft Size Range	AN 12-AN 10
Conductor Size	12 - 10 AWG
Conductor - Copper Str Size	• 12 AWG • 10 AWG
Conductor - Copper Str Size Range	12 AWG-10 AWG
Conductor Type	CU C Str-Size

Configuration



Physical Attribute - Number of Holes	1
Connector Type	Fork Terminal

Dimensions

Package Length	0.000 in
Package Width	0.000 in
Dimension - B Length fraction	2/5 in
Package Weight	0.000 lb.
Dimension - B Length inch	0.41 in
Dimension - Outside Diameter inch	0.22 in
Dimension - Z inch	0.34 in
Dimension - L Length Overall mm	26 mm
Dimension - Pad Width inch	0.47 in
Package Height	0.000 in
Dimension - Bolt Size fraction	1/4
Dimension - Strip Length inch	7/16 in
Dimension - Stud Size inch	1/4 in
Dimension - Length Overall inch	1.03 in
Dimension - D inch	0.59 in
Dimension - N inch	0.25 in

General

Physical Attribute - Tongue Type	Fork
Trade Name	HYLUG™
Plated	Y
Feature - Barrel Type	Standard
Feature - Barrel Style	Chamfered
Type	Fork Tongue
UPC 14 Digit GTIN	00781810025390
Material	Copper
Plating Type	Tin
UPC	781810025390

Logistics

Minimum Pack Quantity	1000
Carton Quantity	1000
Pallet Quantity	99999

Product Assets

[Catalog \[English\]](#)