



YAV10T7, Ring, 14-10 Str, 12-10 Sol, #4-6 Stud

By Burndy
Catalog # [YAV10T7](#)

Seamless Copper Uninsulated Ring, 14-10 Str, 12-10 Str, #4-6 Stud,
Double Thick Tongue, Tin Plated, Bulk Plated, Bulk Package

Features

- Manufactured from seamless pure electrolytic copper tubing to provide maximum conductivity, low resistance and excellent ductility for crimping
- Seamless tubular crimp barrel design - No seams to split resulting in a very high quality electrical connection, also can be used on solid conductor
- Double thick tongue structurally a very strong terminal tongue
- Produced from tubular copper, extra copper material assures the compression connector will operate cooler than the conductors it connects
- Internally bevelled barrel for easy cable entry, especially for flexible conductors
- Inspection hole provides easy visual check for proper conductor insertion
- Electro-tin plated for a long lasting durable corrosion resistance

Application

Industrials, Hospitals, Utilities, Marine, Computer

Specifications

Certification - UL Recognized	No
Buy American Compliant	No
Certification - cULus	No
Industry Standard(s)	• UL467 • Military Specified (Mil-Spec)
Certification - ETL	No
Standards - Industry Standards Met	UL486
Standards - RoHS Compliance	CM
Status	
UL Listed	Yes
Certification - CSA Approved	Yes

Conductor

Conductor - Copper Str Size	• 12 • 10
Conductor Size	12 - 10 AWG
Conductor - Copper Str Navy Size Range	6 (7)-9 (37)
Conductor - Copper Str Navy Size	• 6 (7) • 6 (19) • 9 (7) • 9 (37)
Conductor - Copper Solid Size	• 12 • 11



Conductor - Copper Str Aircraft Size Range	• 10 AN 12-AN 10
Conductor - Copper Str Aircraft Size	• AN 12 • AN 10
Conductor - Copper Solid Size Range	12-10
Conductor Type	• CU C Solid-Size • CU C Str-Size
Conductor - Copper Str Size Range	12 AWG - 10 AWG

Configuration

Physical Attribute - Number of Holes	1
Connector Type	Ring Terminal

Dimensions

Dimension - Pad Width inch	0.31 in
Package Height	0.000 in
Dimension - Hole Size fraction	1/7
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - Outside Diameter inch	0.22 in
Dimension - Stud Size inch	• #4 • #5 • #6
Dimension - Bolt Size fraction	#4 - #6
Dimension - B Length fraction	2/5 in
Dimension - Z inch	0.24 in
Dimension - B Length inch	0.39 in
Dimension - D inch	0.42 in
Dimension - N inch	0.16 in
Dimension - Length Overall inch	0.93 in

General

Product Family	COMPRESSION
Trade Name	HYLUG™
Military Specification	AS20659
Application - For Use On	Copper Commercial (Code) Cable, Type AN Aircraft Cable, Extra Flexible Conductors
Feature - Barrel Type	Standard
Feature - Barrel Style	Chamfered
Plated	Yes
Physical Attribute - Tongue Type	Ring

Sub Brand	HYLUG
Product Type	Terminal
UPC	781810025291
Type	Ring Tongue
Material	Copper
Plating Type	Tin
UPC 14 Digit GTIN	00781810025291

Logistics

Minimum Pack Quantity	500
Pallet Quantity	99999
Carton Quantity	500

Product Assets

[Catalog \[English\]](#)



A Hubbell brand