



YAV10U, Seamless Terminal #10 AWG Undrilled

By Burndy
Catalog # [YAV10U](#)

SEAMLESS UNINSULATED COMPRESSION HEAVY DUTY RING TONGUE TERMINAL.

Features

- Manufactured from seamless pure electrolytic copper tubing to provide maximum conductivity, low resistance and excellent ductility for crimping
- Seamless tubular crimp barrel design - No seams to split resulting in a very high quality electrical connection, also can be used on solid conductor
- Double thick tongue structurally a very strong terminal tongue
- Produced from tubular copper, extra copper material assures the compression connector will operate cooler than the conductors it connects
- Internally bevelled barrel for easy cable entry, especially for flexible conductors
- Inspection hole provides easy visual check for proper conductor insertion
- Electro-tin plated for a long lasting durable corrosion resistance

Specifications

Certification - cULus	N
Certification - UL Recognized	N
Certification - ETL	No
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	NC
Industry Standard(s)	UL467
Certification - CSA Approved	No
UL Listed	No

Conductor

Conductor - Copper Solid Size	• 12 AWG • 11 AWG • 10 AWG
Conductor - Copper Solid Size Range	12 AWG-10 AWG
Conductor - Copper Str Aircraft Size Range	N/A
Conductor - Copper Str Navy Size Range	N/A
Conductor Size	12 - 10 AWG
Conductor - Copper Str Size	• 12 AWG • 10 AWG



Conductor - Copper Str Size Range	12 AWG-10 AWG
Conductor Type	• CU C Solid-Size • CU C Str-Size

Configuration

Connector Type	Ring Terminal
----------------	---------------

Dimensions

Package Length	0.000 in
Package Width	0.000 in
Dimension - B Length fraction	3/8 in
Package Weight	0.000 lb.
Dimension - B Length inch	0.38 in
Dimension - Outside Diameter inch	0.21 in
Dimension - Pad Width inch	0.38 in
Package Height	0.000 in
Dimension - Hole Size mm	0 mm
Dimension - Length Overall inch	0.94 in
Dimension - D inch	0.47 in
Dimension - Thread Size	-

General

Physical Attribute - Tongue Type	Ring
Trade Name	HYLUG
Plated	Y
Feature - Barrel Type	Standard
Feature - Barrel Style	Chamfered
Insulation	N
Type	Ring Tongue
UPC 12 Digit	781810449035
UPC 14 Digit GTIN	00781810449035
Material	Copper
Plating Type	Tin - Electro Plated
UPC	781810449035

Logistics

Minimum Pack Quantity	500
Carton Quantity	500
Pallet Quantity	99999



A Hubbell brand