



YAV14H2, Uninsulated Ring Terminal For 16 - 14 AWG

By Burndy
Catalog # [YAV14H2](#)

Uninsulated Ring Terminal For 16 - 14 AWG



Features

- Manufactured from seamless pure electrolytic copper tubing to provide maximum conductivity, low resistance and excellent ductility for crimping
- Seamless tubular crimp barrel design - No seams to split resulting in a very high quality electrical connection, also can be used on solid conductor
- Double thick tongue structurally a very strong terminal tongue
- Produced from tubular copper, extra copper material assures the compression connector will operate cooler than the conductors it connects
- Internally bevelled barrel for easy cable entry, especially for flexible conductors
- Inspection hole provides easy visual check for proper conductor insertion
- Electro-tin plated for a long lasting durable corrosion resistance

Application

For Use On Copper Commercial (Code) Cable, Type AN Aircraft Cable And Extra Flexible Conductors

Specifications

Buy American Compliant	Contact Manufacturer
Certification - cULus	No
EU RoHS Indicator	Yes
Certification - UL Recognized	No
Industry Standard(s)	UL467
Buy America(n) Qualified	Contact Manufacturer
Certification - ETL	No
Standards - Industry Standards Met	UL486
Standards - RoHS Compliance Status	CM
Certification - CSA Approved	Yes
UL Listed	Yes

Conductor

Conductor - Copper Str Size	• 20 AWG • 18 AWG • 16 AWG • 14 AWG
Conductor Size	16 - 14 AWG

Conductor - Copper Str Size Range	20 AWG - 14 AWG
Conductor Type	• CU C Solid-Size • CU C Str-Size

Configuration

Physical Attribute - Number of Holes	1
Connector Type	Ring Terminal

Dimensions

Package Length	0.000 in
Package Width	0.000 in
Package Weight	0.000 lb.
Dimension - Outside Diameter inch	0.24 in
Dimension - Pad Width inch	0.42 in
Package Height	0.000 in
Dimension - Stud Size inch	1/4
Dimension - B Length fraction	1/4 in
Dimension - B Length inch	0.247 in
Dimension - Z inch	0.32 in
Dimension - Bolt Size fraction	1/4
Dimension - Length Overall inch	1.14 in
Dimension - D inch	0.61 in
Dimension - N inch	0.25 in

General

Trade Name	HYLUG™
Sub Brand	HYLUG
Physical Attribute - Tongue Type	Ring
Plated	Y
Feature - Barrel Type	Standard
Feature - Barrel Style	Shrouded
Type	Ring Tongue
UPC 14 Digit GTIN	00781810024973
Material	Copper
Plating Type	Tin - Electro Plated
UPC	781810024973

Logistics

Minimum Pack Quantity	1000
Carton Quantity	1000

