



YAV14H32F, Uninsulated Fork Terminal For 16 - 14 AWG

By Burndy
Catalog # [YAV14H32F](#)



Uninsulated Fork Terminal For 16 - 14 AWG

Features

- Manufactured from seamless pure electrolytic copper tubing to provide maximum conductivity, low resistance and excellent ductility for crimping
- Seamless tubular crimp barrel design - No seams to split resulting in a very high quality electrical connection, also can be used on solid conductor
- Double thick tongue structurally a very strong terminal tongue
- Produced from tubular copper, extra copper material assures the compression connector will operate cooler than the conductors it connects
- Internally bevelled barrel for easy cable entry, especially for flexible conductors
- Inspection hole provides easy visual check for proper conductor insertion
- Electro-tin plated for a long lasting durable corrosion resistance

Application

For Use On Copper Commercial (Code) Cable, Type AN Aircraft Cable And Extra Flexible Conductors

Specifications

Buy American Compliant	Contact Manufacturer
Certification - cULus	No
EU RoHS Indicator	Yes
Certification - UL Recognized	No
Industry Standard(s)	UL467
Buy America(n) Qualified	Contact Manufacturer
Certification - ETL	No
Standards - Industry Standards Met	UL486
Standards - RoHS Compliance Status	CM
Certification - CSA Approved	Yes
UL Listed	Yes

Conductor

Conductor - Copper Str Size	• 20 AWG • 18 AWG • 16 AWG • 14 AWG
Conductor - Copper Str Aircraft Size	• AN 20 • AN 18

	• AN 16 • AN 14
Conductor - Copper Str Aircraft Size Range	AN 20-AN 14
Conductor - Copper Str Navy Size	• 2 1/2 (1) • 2 1/2 (19) • 2 1/2 (26) • 3 (7) • 4 (1) • 4 (7) • 4 (19) • 4 (41)
Conductor - Copper Str Navy Size Range	2 1/2 (1)-4 (41)
Conductor Size	16 - 14 AWG
Conductor - Copper Str Size Range	20 AWG - 14 AWG
Conductor Type	CU C Str-Size

Configuration

Physical Attribute - Number of Holes	1
Connector Type	Fork Terminal

Dimensions

Dimension - Outside Diameter inch	0.17 in
Dimension - L Length Overall mm	24 mm
Dimension - Pad Width inch	0.30 in
Dimension - Hole Size fraction	3/20
Dimension - Hole Size inch	0.15 in
Dimension - Strip Length inch	1/4 in
Dimension - Stud Size inch	• #4 • #5 • #6
Dimension - B Length fraction	1/4 in
Dimension - B Length inch	0.27 in
Dimension - Z inch	0.23 in
Dimension - Bolt Size fraction	#4 - #6
Dimension - Length Overall inch	0.96 in
Dimension - N inch	0.19 in

General

Trade Name	HYLUG™
------------	--------

Sub Brand	HYLUG	UPC	781810025024
Physical Attribute - Tongue	Fork		
Type		Logistics	
Plated	Y	Minimum Pack Quantity	1000
Feature - Barrel Type	Standard	Carton Quantity	1000
Feature - Barrel Style	Shrouded	Pallet Quantity	99999
Type	Fork Tongue		
UPC 14 Digit GTIN	00781810025024	Product Assets	
Material	Copper	Catalog [English]	
Plating Type	Tin		



A Hubbell brand