



YAV14H56FBOX, Uninsulated Fork Terminal For 16 - 14 AWG

By Burndy
Catalog # [YAV14H56FBOX](#)



Uninsulated Fork Terminal For 16 - 14 AWG

Features

- Manufactured from seamless pure electrolytic copper tubing to provide maximum conductivity, low resistance and excellent ductility for crimping
- Seamless tubular crimp barrel design - No seams to split resulting in a very high quality electrical connection, also can be used on solid conductor
- Double thick tongue structurally a very strong terminal tongue
- Produced from tubular copper, extra copper material assures the compression connector will operate cooler than the conductors it connects
- Internally bevelled barrel for easy cable entry, especially for flexible conductors
- Inspection hole provides easy visual check for proper conductor insertion
- Electro-tin plated for a long lasting durable corrosion resistance

Specifications

Certification - cULus	No
Certification - UL Recognized	No
Certification - ETL	No
Standards - Industry Standards Met	UL486
Standards - RoHS Compliance Status	CM
Certification - CSA Approved	Yes
UL Listed	Yes

Conductor

Conductor - Copper Str Aircraft Size	• AN 20 • AN 18 • AN 16 • AN 14
Conductor - Copper Str Aircraft Size Range	AN 20-AN 14
Conductor Size	16 - 14 AWG
Conductor - Copper Str Size	• 20 AWG • 18 AWG • 16 AWG • 14 AWG
Conductor - Copper Str Size Range	20 AWG - 14 AWG
Conductor Type	CU C Str-Size

Configuration

Physical Attribute - Number of Holes	1
Connector Type	Fork Terminal

Dimensions

Dimension - B Length fraction	1/4 in
Dimension - B Length inch	0.27 in
Dimension - Outside Diameter inch	0.17 in
Dimension - Z inch	0.23 in
Dimension - L Length Overall mm	24 mm
Dimension - Pad Width inch	0.30 in
Dimension - Hole Size fraction	8/47
Dimension - Bolt Size fraction	#6 - #8
Dimension - Hole Size inch	0.17 in
Dimension - Strip Length inch	1/4 in
Dimension - Stud Size inch	• #6 • #8
Cable Insulation Diameter Maximum	0.150 in
Dimension - Length Overall inch	0.96 in
Dimension - N inch	0.19 in

General

Physical Attribute - Tongue Type	Fork
Trade Name	HYLUG™
Plated	Y
Feature - Barrel Type	Standard
Feature - Barrel Style	Shrouded
Type	Fork Tongue
UPC 12 Digit	781810532706
UPC 14 Digit GTIN	00781810532706
Material	Copper
Plating Type	Tin
UPC	781810532706

Logistics

Minimum Pack Quantity	100
Carton Quantity	1200



A Hubbell brand