



Oh No!
IMAGE COMING SOON

YAV14NKBOX, Seamless Uninsulated
Compression Heavy Duty Ring Tongue
Terminal, 16 - 14 AWG, Nickel Plated

By Burndy
Catalog # YAV14NKBOX

SEAMLESS UNINSULATED COMPRESSION HEAVY DUTY RING
TONGUE TERMINAL.

Specifications

Certification - ETL	No
Certification - UL Recognized	N
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	CM
Certification - cULus	N
Industry Standard(s)	UL467
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor Size	16 - 14 AWG
Conductor - Copper Str Navy Size Range	N/A
Conductor - Copper Solid Size	20 18 AWG 17 AWG 16 AWG 15 AWG 14 AWG
Conductor - Copper Str Aircraft Size Range	N/A
Conductor - Copper Solid Size Range	20 -14 AWG
Conductor Type	- CU C Solid-Size - CU C Str-Size
Conductor - Copper Str Size Range	20 AWG-14 AWG
Conductor - Copper Str Size	20 AWG 18 AWG 16 AWG 14 AWG

Configuration

Physical Attribute - Number of Holes	1
Connector Type	Ring Terminal

Dimensions

Dimension - Pad Width inch	0.29 in
Package Height	0.000 in
Dimension - Bolt Size fraction	#8 - #10
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - Z inch	0.24 in
Dimension - L Length Overall mm	20 mm
Dimension - Thread Size	-
Dimension - Length Overall inch	0.79 in
Dimension - Stud Size inch	#8 #10

General

Feature - Barrel Type	Standard
Feature - Barrel Style Plated	Chamfered Y
Trade Name	HYLUG
Physical Attribute - Tongue Type	Ring
UPC	781810147597
Type	Ring Tongue
Insulation	N
Material	Copper
Plating Type	Nickel
UPC 12 Digit	781810147597
UPC 14 Digit GTIN	00781810147597

Logistics

Pallet Quantity	99999
Carton Quantity	1200

Product Assets

[Catalog \[English\]](#)