



YAV1502M12, Compression Terminal

By Burndy

Catalog # [YAV1502M12](#)

Copper Compression Terminal



Features

- Barrel is designed with an internal chamfer at the wire entry to ensure smooth insertion of the wire, preventing possible damaging of the strands
- Electro-tin plated unless otherwise specified to reduce galvanic corrosion (bimetallic) and resist corrosive elements
- Connectors are clearly marked with stamping
- Compatible Standards: IEC61238-1, UL 486A-486B, CSA-C22.2 No. 65-03

Application

Metric Wire Termination

Specifications

Certification - UL Recognized	No
Certification - cULus	No
Certification - ETL	No
Standards - RoHS Compliance	CM
Status	
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - Material	COPPER
Conductor - Copper Str Size	150 mm ²
Conductor - Copper DLO Size	N/A
Range	
Conductor Size	150 mm ²
Conductor Type	CLASS 2
Conductor - Copper Str Size	300 kcmil
Range	

Configuration

Physical Attribute - Number of Holes	2
Number of Pad Holes	2
Connector Type	METRIC

Current

Voltage Rating	35 kV
Voltage - Maximum	35000

Dimensions

Dimension - Pad Width inch	30.5 in
----------------------------	---------

Package Height	0.000 in
Dimension - Hole Size fraction	1/2
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall	113 mm
mm	
Dimension - Outside Diameter	0.88 in
inch	
Dimension - Hole Size mm	13.5 mm
Dimension - Hole Size inch	0.53
Dimension - Strip Length inch	1.06 in
Dimension - Stud Size fraction	1/2
Dimension - Bolt Size fraction	1/2
Physical Attribute - Tongue	Straight
Angle	
Dimension - B Length fraction	1-3/50 in
Dimension - Z inch	0.55 in
Dimension - B Length inch	26.2 in
Dimension - D inch	2.66 in
Dimension - N inch	0.53 in
Dimension - Bolt Size inch	0.5
Dimension - Length Overall	4.45 in
inch	

General

Trade Name	HYLUG™
Die Index	17
Plated	Y
UPC	781810442739
Type	Metric Terminals
Material	Copper
Plating Type	Tin - Electro Plated
Finish Type	Tin-Plated
UPC 12 Digit	781810442739
UPC 14 Digit GTIN	00781810442739

Logistics

Minimum Pack Quantity	10
Carton Quantity	10

Operational

Temperature Rating	194
--------------------	-----



A Hubbell brand