



YAV18T21F, Uninsulated Fork Terminal For 22 - 18 AWG

By Burndy
Catalog # [YAV18T21F](#)

Uninsulated Fork Terminal For 22 - 18 AWG



Features

- Manufactured from seamless pure electrolytic copper tubing to provide maximum conductivity, low resistance and excellent ductility for crimping
- Seamless tubular crimp barrel design - No seams to split resulting in a very high quality electrical connection, also can be used on solid conductor
- Double thick tongue structurally a very strong terminal tongue
- Produced from tubular copper, extra copper material assures the compression connector will operate cooler than the conductors it connects
- Internally bevelled barrel for easy cable entry, especially for flexible conductors
- Inspection hole provides easy visual check for proper conductor insertion
- Electro-tin plated for a long lasting durable corrosion resistance

Specifications

Certification - cULus	No
Certification - UL Recognized	No
Certification - ETL	No
Standards - Industry Standards Met	UL486
Standards - RoHS Compliance Status	CM
Industry Standard(s)	UL467
Certification - CSA Approved	Yes
UL Listed	Yes

Conductor

Conductor - Copper Str Aircraft Size	• AN 22 • AN 20 • AN 18
Conductor - Copper Str Aircraft Size Range	AN 22-AN 18
Conductor Size	22 - 18 AWG
Conductor - Copper Str Size	• 22 AWG • 20 AWG • 18 AWG
Conductor - Copper Str Size Range	22 AWG - 18 AWG
Conductor Type	CU C Str-Size

Configuration

Physical Attribute - Number of Holes	1
Connector Type	Fork Terminal

Dimensions

Package Length	0.000 in
Package Width	0.000 in
Dimension - B Length fraction	1/4"
Package Weight	0.000 lb.
Dimension - B Length inch	0.27 in
Dimension - Outside Diameter inch	0.12 in
Dimension - Z inch	0.25 in
Dimension - L Length Overall mm	21 mm
Dimension - Pad Width inch	0.37 in
Package Height	0.000 in
Dimension - Bolt Size fraction	#8 - #10
Dimension - Strip Length inch	9/32 in
Dimension - Stud Size inch	• #8 • #9 • #10
Dimension - Length Overall inch	0.84 in
Dimension - D inch	0.50 in
Dimension - N inch	0.25 in

General

Physical Attribute - Tongue Type	Fork
Trade Name	HYLUG™
Plated	Y
Feature - Barrel Type	Standard
Feature - Barrel Style	Chamfered
Type	Fork Tongue
UPC 12 Digit	781810025437
UPC 14 Digit GTIN	00781810025437
Material	Copper
Plating Type	Tin - Electro Plated
UPC	781810025437

Logistics

Minimum Pack Quantity	1000
Carton Quantity	1000

