



YAV1CL, Ring Terminal, 1 AWG, 1-Hole, 3/8" Stud

By Burndy
Catalog # [YAV1CL](#)

Seamless Uninsulated Ring, 1 AWG, 1-Hole, 3/8" Stud, Double Thick Tongue, Tin Plated

Features

- Manufactured from seamless pure electrolytic copper tubing to provide maximum conductivity, low resistance and excellent ductility for crimping
- Seamless tubular crimp barrel design - No seams to split resulting in a very high quality electrical connection, also can be used on solid conductor
- Double thick tongue structurally a very strong terminal tongue
- Produced from tubular copper, extra copper material assures the compression connector will operate cooler than the conductors it connects
- Internally bevelled barrel for easy cable entry, especially for flexible conductors
- Inspection hole provides easy visual check for proper conductor insertion
- Electro-tin plated for a long lasting durable corrosion resistance

Application

For Use On Type AN Aircraft Cable, Extra Flexible Conductors And Commercial (Code) Conductors, Industrials, Hospitals, Electric Utilities, Marine, Computers, And Other Equipment Subject To Vibration Or Requiring Dependable Electrical Performance

Specifications

Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL467
Certification - ETL	No
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance	CM
Status	
UL Listed	Yes
Certification - CSA Approved	Yes

Conductor

Conductor - Copper Str Size	1
Conductor Size	1 AWG
Conductor - Copper Str Aircraft Size Range	AN 1
Conductor - Copper Str Aircraft Size	AN 1
Conductor Type	• CU C Solid-Size • CU C Str-Size
Conductor - Copper Str Size Range	1 AWG



Configuration

Physical Attribute - Number of Holes	1
Connector Type	Ring Terminal

Dimensions

Dimension - Pad Width inch	0.76 in
Package Height	0.000 in
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - Outside Diameter inch	0.51 in
Dimension - Hole Size mm	10 mm
Dimension - Hole Size inch	0.40 in
Dimension - Strip Length inch	5/8
Dimension - Bolt Hole Size inch	0.39 in
Dimension - Bolt Size fraction	3/8
Physical Attribute - Tongue Angle	Straight
Dimension - B Length fraction	5/8 in
Dimension - Z inch	0.38 in
Dimension - B Length inch	0.60 in
Dimension - D inch	0.76 in
Dimension - N inch	0.38 in
Dimension - Length Overall inch	1.84 in

General

Material Composition	• DLP Copper • Tin Plating
Product Family	COMPRESSION
Trade Name	HYLUG™
Die Index	42
Feature - Barrel Type	Standard
Feature - Barrel Style	• Chamfered • Skived
Plated	Yes
Physical Attribute - Tongue Type	Ring
Sub Brand	HYLUG
Product Type	Terminal
UPC	781810025475
Type	Ring Tongue
Material	Copper
Plating Type	Tin
UPC 14 Digit GTIN	00781810025475

Logistics

Pallet Quantity

46400

Carton Quantity

200

Product Assets

[Catalog \[English\]](#)



A Hubbell brand