



YAV1CLBOX, Uninsulated Ring Terminal For 1 AWG, 1-Hole, 3/8" Stud

By Burndy
Catalog # [YAV1CLBOX](#)

Uninsulated Ring Terminal For 1 AWG



Features

- Manufactured from seamless pure electrolytic copper tubing to provide maximum conductivity, low resistance and excellent ductility for crimping
- Seamless tubular crimp barrel design - No seams to split resulting in a very high quality electrical connection, also can be used on solid conductor
- Double thick tongue structurally a very strong terminal tongue
- Produced from tubular copper, extra copper material assures the compression connector will operate cooler than the conductors it connects
- Internally bevelled barrel for easy cable entry, especially for flexible conductors
- Inspection hole provides easy visual check for proper conductor insertion
- Electro-tin plated for a long lasting durable corrosion resistance

Specifications

Certification - cULus	No
Certification - UL Recognized	No
Industry Standard(s)	UL467
Certification - ETL	No
Standards - Industry Standards Met	UL486
Standards - RoHS Compliance Status	CM
Certification - CSA Approved	Yes
UL Listed	Yes

Conductor

Conductor - Copper Str Size	1
Conductor - Copper Str Aircraft Size	AN 1
Conductor - Copper Str Aircraft Size Range	AN 1
Conductor Size	1 AWG
Conductor - Copper Str Size Range	1 AWG
Conductor Type	• CU C Solid-Size • CU C Str-Size

Configuration

Physical Attribute - Number of Holes	1
Connector Type	Ring Terminal

Dimensions

Package Length	0.000 in
Package Width	0.000 in
Package Weight	0.000 lb.
Dimension - Outside Diameter inch	0.51 in
Dimension - Pad Width inch	0.76 in
Package Height	0.000 in
Dimension - Hole Size mm	10 mm
Dimension - Strip Length inch	5/8 in
Dimension - Stud Size inch	3/8 in
Dimension - B Length fraction	5/8 in
Dimension - B Length inch	0.60 in
Dimension - Z inch	0.38 in
Physical Attribute - Tongue Angle	Straight
Dimension - Bolt Hole Size inch	0.39 in
Dimension - Bolt Size fraction	3/8
Dimension - Length Overall inch	1.84 in
Dimension - D inch	0.76 in
Dimension - N inch	0.38 in

General

Die Index	42
Trade Name	HYLUG™
Material Composition	• DLP Copper • Tin Plating
Physical Attribute - Tongue Type	Ring
Plated	Y
Feature - Barrel Type	Standard
Feature - Barrel Style	• Chamfered • Skived
Type	Ring Tongue
UPC 14 Digit GTIN	00781810539859
Material	Copper
Plating Type	Tin
UPC	781810539859

Logistics

Minimum Pack Quantity	1
-----------------------	---



A Hubbell brand