



YAV252TC14FXB, Compression Terminal, 1/0 Flex G,H,I,K,M, DLO, 1/0 AWG B/C, Cu, 2-Hole, 1/4" Stud, 5/8" Spacing, Long Barrel

By Burndy

Catalog # [YAV252TC14FXB](#)

1/0 Flex G,H,I,K,M,DLO, 1/0 AWG (B/C), CU, 2 Hole, 1/4 Stud, 5/8
IN Spacing, Long Barrel, Bell End

Application

Wire Termination

Specifications

Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL 486A-486B
Certification - ETL	No
Standards - RoHS Compliance Status	CM
UL Listed	Yes
Certification - CSA Approved	Yes

Conductor

Conductor - Material	COPPER
Wire Size	1/0 AWG
Conductor - Copper Flex K Size Range	1/0 AWG
Conductor - Copper Flex K Size	"1/0 AWG"
Conductor - Copper Flex M Size Range	1/0 AWG
Conductor - Copper Flex M Size	"1/0 AWG"
Conductor - Copper Str Size	"1/0 AWG"
Conductor - Copper Flex I Size Range	1/0 AWG
Conductor - Copper Flex G Size	"1/0 AWG"
Conductor - Copper DLO Size Range	1/0 AWG
Conductor - Copper Str Compact Size	"1/0 AWG"
Conductor - Copper DLO Size	1/0 AWG
Conductor Size	1/0 AWG
Conductor - Copper Flex H Size	"1/0 AWG"
Conductor - Copper Flex G Size Range	1/0 AWG
Conductor - Copper Str Navy Size	100
Conductor Type	CODE/FLEX
Conductor - Copper Str Size Range	1/0 AWG
Conductor - Copper Flex H Size Range	1/0 AWG
Conductor - Copper Flex I Size	"1/0 AWG"

Configuration



Physical Attribute - Number of Holes	2
Connector Type	LONG BARREL

Current

Voltage Rating	35 kV
Voltage - Maximum	35000

Dimensions

Dimension - Pad Width inch	0.83 in
Package Height	0.000 in
Dimension - Hole Size fraction	1/4
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall mm	82 mm
Dimension - Outside Diameter inch	0.56 in
Dimension - Hole Size mm	6.9 mm
Dimension - Hole Size inch	0.27 in
Dimension - Strip Length inch	1-9/16
Dimension - Stud Size inch	1/4
Dimension - Stud Size fraction	1/4
Dimension - Bolt Hole Size inch	0.27 in
Dimension - Bolt Size fraction	1/4
Physical Attribute - Tongue Angle	Straight
Dimension - Z inch	0.33 in
Dimension - B Length inch	1.50 in
Dimension - D inch	1.5
Dimension - N inch	0.31 in
Dimension - Bolt Size inch	0.25
Dimension - Length Overall inch	3.21 in

General

Trade Name	HYLUG™
Die Index	12
Feature - Barrel Type	Long
Feature - Barrel Style	Belled
Plated	Y
Color Code	Pink
Physical Attribute - Tongue Type	Standard

UPC	781810307182
Type	Long Barrel, Tin Plated
Material	COPPER
Plating Type	Tin - Electro Plated
Finish Type	Tin-Plated
UPC 12 Digit	781810307182
UPC 14 Digit GTIN	00781810307182

Logistics

Pallet Quantity	24000
Carton Quantity	25

Product Assets

- [Catalog \[English\]](#)
- [Installation Manual \[English\]](#)
- [Installation Manual \[French, English\]](#)



A Hubbell brand