



**YAV25L2NT14FX90, Compression Terminal,
1/0 Flex G, H, I, K, M, DLO, 1/0 AWG (B/C),
CU, 2-Hole, 1/4" Stud, 5/8" Spacing, Narrow
Tongue, 90 Degree**

By Burndy
Catalog # [YAV25L2NT14FX90](#)

1/0 Flex G,H,I,K,M,DLO, 1/0 AWG (B/C), CU, 2 Hole, 1/4 Stud, 5/8
IN Spacing, Standard Barrel, Inspection Window, Narrow Tongue,
90 Degree

Features

- Electro-tin plated unless otherwise specified to reduce galvanic corrosion (bimetallic) and resist corrosive elements
- Connectors are clearly marked with stamping and barrel color coding
- For applications greater than 2000 Volts consult cable manufacturer for voltage stress relief instructions

Application

Wire Termination

Specifications

Certification - UL Recognized	No
Buy American Compliant	No
Certification - cULus	No
EU RoHS Indicator	Contact Manufacturer
Industry Standard(s)	UL 486A-486B
Certification - ETL	No
Standards - RoHS Compliance	CM
Status	
UL Listed	Yes
Certification - CSA Approved	Yes

Conductor

Conductor - Material	COPPER
Wire Size	1/0 AWG
Conductor - Copper Flex K Size	1/0 AWG
Range	
Conductor - Copper Flex K Size	"1/0 AWG"
Conductor - Copper Flex M Size	"1/0 AWG"
Conductor - Copper Str Size	"1/0 AWG"
Conductor - Copper Flex I Size	1/0 AWG
Range	
Conductor - Copper Flex G Size	"1/0 AWG"
Conductor - Copper DLO Size	1/0 AWG
Range	
Conductor - Copper Str	"1/0 AWG"
Compact Size	
Conductor - Copper DLO Size	1/0 AWG
Conductor Size	1/0 AWG
Conductor - Copper Flex H Size	"1/0 AWG"



Conductor - Copper Flex G Size	1/0 AWG
Range	
Conductor - Copper Str Navy	100 (61) Navy
Size Range	
Conductor - Copper Str Navy	100
Size	
Conductor Type	CODE/FLEX
Conductor - Copper Str Size	1/0 AWG
Range	
Conductor - Copper Flex H Size	1/0 AWG
Range	
Conductor - Copper Flex I Size	"1/0 AWG"

Configuration

Number of Holes	2
Physical Attribute - Number of Holes	2
Number of Pad Holes	2
Connector Type	STANDARD BARREL

Current

Voltage Rating	35 kV
Voltage - Maximum	35000

Dimensions

Dimension - Pad Width inch	0.64 in
Package Height	0.000 in
Dimension - Hole Size fraction	1/4
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall mm	42 mm
Dimension - Outside Diameter inch	0.56 in
Dimension - Hole Size mm	6.9 mm
Dimension - Hole Size inch	0.27
Dimension - Strip Length inch	11/16 in
Dimension - Stud Size inch	1/4 in
Dimension - Stud Size fraction	1/4
Dimension - Bolt Hole Size inch	0.27 in
Dimension - Bolt Size fraction	1/4

Physical Attribute - Tongue Angle	90 Degree	Color Code	Pink
Angle - Pad	90 °	Sub Brand	HYLUG
Dimension - B Length fraction	11/16 in	UPC	781810660843
Dimension - B Length inch	0.69 in	Type	Narrow Tongue
Dimension - N inch	0.31 in	Construction Material - Main	Copper
Dimension - Bolt Size inch	0.25	Material	Copper
Dimension - Length Overall	1.66 in	Plating Type	Tin
inch		Finish Type	Tin-Plated
		UPC 14 Digit GTIN	00781810660843

General

Trade Name	HYLUG™
Die Index	12
Color	Pink
Feature - Barrel Type	Standard
Feature - Barrel Style	• Chamfered • Skived

PlatedY



A Hubbell brand

Logistics

Minimum Pack Quantity	1
Pallet Quantity	24000
Carton Quantity	25

Product Assets

[Catalog \[English\]](#)