



YAV25LTC38FX90, Compression Terminal, 1/0 Flex G,H,I,K,M, DLO, 1/0 AWG, Cu, 1- Hole, 3/8" Stud, Standard Barrel, 90 Degree

By Burndy

Catalog # [YAV25LTC38FX90](#)

1/0 Flex G,H,I,K,M,DLO, 1/0 AWG, CU, 1 Hole, 3/8 Stud, Standard
Barrel, Inspection Window, 90 degree

Features

- Electro-tin plated unless otherwise specified to reduce galvanic corrosion (bimetallic) and resist corrosive elements
- Connectors are clearly marked with stamping and barrel color coding
- For applications greater than 2000 Volts consult cable manufacturer for voltage stress relief instructions

Application

Wire Termination

Specifications

Certification - UL Recognized	No
Buy American Compliant	Contact Manufacturer
Certification - cULus	No
EU RoHS Indicator	Yes
Buy America(n) Qualified	Contact Manufacturer
Industry Standard(s)	UL 486A-486B
Certification - ETL	No
Standards - RoHS Compliance	CM
Status	
UL Listed	Yes
Certification - CSA Approved	Yes

Conductor

Conductor - Material	COPPER
Wire Size	1/0 AWG
Conductor - Copper Flex K Size	1/0 AWG
Range	
Conductor - Copper Flex K Size	"1/0 AWG"
Conductor - Copper Flex M Size	1/0 AWG
Range	
Conductor - Copper Flex M Size	"1/0 AWG"
Conductor - Copper Str Size	"1/0 AWG"
Conductor - Copper Flex I Size	1/0 AWG
Range	
Conductor - Copper Flex G Size	"1/0 AWG"
Conductor - Copper DLO Size	1/0 AWG
Range	
Conductor - Copper Str	"1/0 AWG"
Compact Size	
Conductor - Copper DLO Size	1/0 AWG
Conductor Size	1/0 AWG



Conductor - Copper Flex H Size	"1/0 AWG"
Conductor - Copper Flex G Size	1/0 AWG
Range	
Conductor - Copper Str Navy	100 (61) Navy
Size Range	
Conductor - Copper Str Navy	100
Size	
Conductor - Copper Solid Size	1/0 AWG
Conductor - Copper Solid Size	1/0 AWG
Range	
Conductor - CopperWeld Str	1/0 WELD
Size Range	
Conductor - CopperWeld Str	1/0 WELD
Size	
Conductor Type	CODE/FLEX
Conductor - Copper Str Size	1/0 AWG
Range	
Conductor - Copper Flex H Size	1/0 AWG
Range	
Conductor - Copper Flex I Size	"1/0 AWG"

Configuration

Physical Attribute - Number of Holes	1
Number of Pad Holes	1
Connector Type	STANDARD BARREL

Current

Voltage Rating	35 kV
Voltage - Maximum	35000

Dimensions

Dimension - Pad Width inch	0.83 in
Package Height	0.000 in
Dimension - Height mm	33.3 mm
Dimension - Hole Size fraction	3/8
Dimension - Height inch	1.31 in
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall mm	31 mm
Dimension - Outside Diameter inch	0.56 in

Dimension - Hole Size mm	10.4 mm	Color Code	Pink
Dimension - Hole Size inch	0.41	Physical Attribute - Tongue	Standard
Dimension - Strip Length inch	11/16 in	Type	
Dimension - Stud Size fraction	3/8	Sub Brand	TERMINALS, HYLUG
Dimension - Bolt Hole Size inch	0.40 in	UPC	781810022740
Dimension - Bolt Size fraction	3/8	Type	Standard Barrel, Tin Plated
Physical Attribute - Tongue	90 Degree	Material	Copper
Angle		Plating Type	Tin
Angle - Pad	90 °	Finish Type	Tin-Plated
Dimension - B Length fraction	11/16 in	UPC 12 Digit	781810022740
Dimension - Z inch	0.42 in	UPC 14 Digit GTIN	00781810022740
Dimension - B Length inch	0.69 in		
Dimension - N inch	0.41 in		
Dimension - Bolt Size inch	0.38		
Dimension - Length Overall	1.22 in		
inch			
General		Logistics	
Trade Name	HYLUG™	Minimum Pack Quantity	1
Die Index	12	Pallet Quantity	24000
Feature - Barrel Type	Standard	Carton Quantity	25
Feature - Barrel Style	Chamfered		
Plated	Y	Operational	
		Temperature Rating	194
		Product Assets	
		Catalog [English]	

