



YAV26L12BR, Uninsulated Ring Terminal For 2/0 AWG, 1-Hole, 5/8" Stud

By Burndy
Catalog # [YAV26L12BR](#)

Uninsulated Ring Terminal For 2/0 AWG

Features

- Manufactured from seamless pure electrolytic copper tubing to provide maximum conductivity, low resistance and excellent ductility for crimping
- Seamless tubular crimp barrel design - No seams to split resulting in a very high quality electrical connection, also can be used on solid conductor
- Double thick tongue structurally provides for a very strong terminal tongue
- Produced from tubular copper, extra copper material assures the compression connector will operate cooler than the conductors it connects
- Internally bevelled barrel for easy cable entry, especially for flexible conductors
- Inspection hole provides easy visual check for proper conductor insertion
- Electro-tin plated for a long lasting durable corrosion resistance

Specifications

Certification - cULus	No
Certification - UL Recognized	No
Certification - ETL	No
Standards - Industry Standards Met	UL486
Standards - RoHS Compliance Status	CM
Certification - CSA Approved	Yes
UL Listed	Yes

Conductor

Conductor - Copper Str Aircraft Size	AN 00
Conductor - Copper Str Aircraft Size Range	AN 00
Conductor Size	2/0 AWG
Conductor Type	• CU C Solid-Size • CU C Str-Size

Configuration



Physical Attribute - Number of Holes	1
Connector Type	Ring Terminal

Dimensions

Dimension - B Length fraction	3/4 in
Dimension - B Length inch	0.78 in
Dimension - Z inch	0.62 in
Dimension - Pad Width inch	0.93 in
Physical Attribute - Tongue Angle	Straight
Dimension - Bolt Hole Size inch	0.66 in
Dimension - Bolt Size fraction	5/8
Dimension - Hole Size mm	17 mm
Dimension - Strip Length inch	13/16
Dimension - Stud Size inch	5/8 in
Dimension - Length Overall inch	2.52 in
Dimension - D inch	1.15 in
Dimension - N inch	0.53 in

General

Die Index	44
Physical Attribute - Tongue Type	Ring
Trade Name	HYLUG™
Plated	Y
Feature - Barrel Type	Standard
Feature - Barrel Style	Chamfered
Type	Ring Tongue
UPC 14 Digit GTIN	00781810100639
Material	Copper
Plating Type	Unplated HYDENT
UPC	781810100639

Logistics

Minimum Pack Quantity	100
Carton Quantity	100
Pallet Quantity	29600

Product Assets

[Catalog \[English\]](#)