



YAV26L12NK, Compression Terminal, 2/0 AWG, 1-Hole, 5/8" Stud, Standard Barrel, Nickel Plated

By Burndy
Catalog # [YAV26L12NK](#)

Copper Compression Terminal

Features

- Seamless, heavy duty uninsulated compression terminal provides a strong connector for demanding applications requiring high reliability
- Suitable for use on Type AN aircraft cable, extra flexible conductors and commercial (code) conductors

Application

Wire Termination

Specifications

Standards - RoHS Compliance	CM
Status	
Industry Standard(s)	UL 486A-486B
UL Listed	Yes
Certification - CSA Approved	Yes

Conductor

Conductor Size	2/0 AWG
Conductor - Copper Str Aircraft Size	AN 00
Conductor - Material	COPPER
Conductor Type	CODE
Conductor - Copper Str Size	2/0 AWG

Configuration

Physical Attribute - Number of Holes	1
Number of Pad Holes	1
Connector Type	STANDARD BARREL

Current

Voltage Rating	35 kV
Voltage - Maximum	35000

Dimensions

Dimension - Pad Width inch	0.934 in
Package Height	0.000 in



Dimension - Hole Size fraction	1/2
Dimension - Bolt Size fraction	1/2
Physical Attribute - Tongue Angle	Straight
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - Z inch	0.621 in
Dimension - B Length inch	0.782 in
Dimension - N inch	0.53 in
Dimension - Hole Size mm	13.5 mm
Dimension - Bolt Size inch	0.5
Dimension - Hole Size inch	0.53
Dimension - Length Overall inch	2.523 in
Dimension - Strip Length inch	13/16 in
Dimension - Stud Size fraction	1/2

General

Feature - Barrel Type	Standard
Feature - Barrel Style	Chamfered
Plated	Yes
Trade Name	HYLUG™
Physical Attribute - Tongue Type	Ring
Die Index	13
UPC	781810069851
Type	Standard Barrel, Nickel Plated
Material	Copper
Plating Type	Nickel
Finish Type	Nickel Plated
UPC 12 Digit	781810069851
UPC 14 Digit GTIN	00781810069851

Logistics

Pallet Quantity	29600
Carton Quantity	100

Product Assets

[Catalog \[English\]](#)