



YAV26L22, Uninsulated Ring Terminal For 2/0 AWG, 1-Hole, 3/4" Stud

By Burndy

Catalog # [YAV26L22](#)

Uninsulated Ring Terminal For 2/0 AWG



Features

- Manufactured from seamless pure electrolytic copper tubing to provide maximum conductivity, low resistance and excellent ductility for crimping
- Seamless tubular crimp barrel design - No seams to split resulting in a very high quality electrical connection, also can be used on solid conductor
- Double thick tongue structurally a very strong terminal tongue
- Produced from tubular copper, extra copper material assures the compression connector will operate cooler than the conductors it connects
- Internally bevelled barrel for easy cable entry, especially for flexible conductors
- Inspection hole provides easy visual check for proper conductor insertion
- Electro-tin plated for a long lasting durable corrosion resistance

Specifications

Certification - cULus	No
Certification - UL Recognized	No
Industry Standard(s)	UL467
Certification - ETL	No
Standards - Industry Standards Met	UL486
Standards - RoHS Compliance Status	CM
Certification - CSA Approved	Yes
UL Listed	Yes

Conductor

Conductor - Copper Str Size	2/0 AWG
Conductor - Copper Str Aircraft Size	AN 00
Conductor - Copper Str Aircraft Size Range	AN 00
Conductor Size	2/0 AWG
Conductor - Copper Str Size Range	2/0 AWG
Conductor Type	• CU C Solid-Size • CU C Str-Size

Configuration

Physical Attribute - Number of Holes	1
Connector Type	Ring Terminal

Dimensions

Package Length	0.000 in
Package Width	0.000 in
Package Weight	0.000 lb.
Dimension - Pad Width inch	1.12 in
Package Height	0.000 in
Dimension - Hole Size mm	20 mm
Dimension - Stud Size inch	3/4 in
Dimension - B Length fraction	3/4 in
Dimension - B Length inch	0.78 in
Dimension - Z inch	0.79 in
Physical Attribute - Tongue Angle	Straight
Dimension - Bolt Hole Size inch	0.91 in
Dimension - Bolt Size fraction	3/4
Dimension - Length Overall inch	2.66 in
Dimension - D inch	1.29 in
Dimension - N inch	0.5 in

General

Die Index	44
Trade Name	HYLUG™
Material Composition	• DLP Copper • Tin Plating
Physical Attribute - Tongue Type	Ring
Plated	Y
Feature - Barrel Type	Standard
Feature - Barrel Style	Chamfered
Type	Ring Tongue
UPC 14 Digit GTIN	00781810025703
Material	Copper
Plating Type	Tin
UPC	781810025703

Logistics

Minimum Pack Quantity	100
Carton Quantity	100
Pallet Quantity	29600



A Hubbell brand