



YAV26L2TC12E1FX, Compression Terminal,
2/0 Flex G,H,I,K,M, DLO, 2/0 AWG, Cu, 2-
Hole, 1/2" Stud, 1" Spacing, Standard Barrel

By Burndy
Catalog # [YAV26L2TC12E1FX](#)

2/0 Flex G,H,I,K,M,DLO, 2/0 AWG, CU, 2 Hole, 1/2 Stud, 1 IN
Spacing, Standard Barrel, Inspection Window

Features

- Electro-tin plated unless otherwise specified to reduce galvanic corrosion (bimetallic) and resist corrosive elements
- Connectors are clearly marked with stamping and barrel color coding
- For applications greater than 2000 Volts consult cable manufacturer for voltage stress relief instructions

Application

Wire Termination

Specifications

Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL 486A-486B
Certification - ETL	No
Standards - RoHS Compliance	CM
Status	
UL Listed	Yes
Certification - CSA Approved	Yes

Conductor

Conductor - Material	COPPER
Wire Size	2/0 AWG
Conductor - Copper Flex K Size	2/0 AWG
Range	
Conductor - Copper Flex K Size	"2/0 AWG"
Conductor - Copper Flex M Size	"2/0 AWG"
Conductor - Copper Str Size	"2/0 AWG"
Conductor - Copper Flex I Size	2/0 AWG
Range	
Conductor - Copper Flex G Size	"2/0 AWG"
Conductor - Copper DLO Size	2/0 AWG
Range	
Conductor - Copper Str	"2/0 AWG"
Compact Size	
Conductor - Copper DLO Size	2/0 AWG
Conductor Size	2/0 AWG
Conductor - Copper Flex H Size	"2/0 AWG"
Conductor - Copper Flex G Size	2/0 AWG
Range	
Conductor - Copper Str Navy	125
Size	



Conductor - CopperWeld Str Size	• 2/0 F AWG • 2/0 G AWG • 2/0 J AWG • 2/0 K AWG • 2/0 V AWG
---------------------------------	---

Conductor Type	CODE/FLEX
Conductor - Copper Str Size	2/0 AWG
Range	
Conductor - Copper Flex H Size	2/0 AWG
Range	
Conductor - Copper Flex I Size	"2/0 AWG"

Configuration

Physical Attribute - Number of Holes	2
Number of Pad Holes	2
Connector Type	STANDARD BARREL

Current

Voltage Rating	35 kV
Voltage - Maximum	35000

Dimensions

Dimension - Pad Width inch	0.93 in
Package Height	0.000 in
Dimension - Height mm	0 mm
Dimension - Hole Size fraction	1/2
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall	86 mm
mm	
Dimension - Outside Diameter	0.63 in
inch	
Dimension - Hole Size mm	13.5 mm
Dimension - Hole Size inch	0.53
Dimension - Strip Length inch	13/16 in
Dimension - Stud Size fraction	1/2
Dimension - Bolt Hole Size inch	0.52 in
Dimension - Bolt Size fraction	1/2
Physical Attribute - Tongue	Straight
Angle	
Dimension - Z inch	0.56 in
Dimension - B Length inch	0.81 in
Dimension - N inch	0.53 in

Dimension - Bolt Size inch	0.5	Material	Copper
Dimension - Length Overall inch	3.37 in	Plating Type	Tin
General		Finish Type	Tin-Plated
		UPC 12 Digit	781810021774
		UPC 14 Digit GTIN	00781810021774
	Trade Name	HYLUG™	
Die Index	13	Logistics	
Feature - Barrel Type	Standard	Minimum Pack Quantity	100
Feature - Barrel Style	• Chamfered • Skived	Pallet Quantity	18500
Plated	Yes	Carton Quantity	100
Color Code	Black	Product Assets	
Physical Attribute - Tongue	Standard	Catalog [English]	
Type		Installation Manual [English]	
UPC	781810021774	Installation Manual [English]	
Type	Standard Barrel, Tin Plated		

