



YAV26L2TC38FX, Cu Compression, 2-Hole, 3/8" Stud, 1" Spacing, Standard Barrel, 2/0 Flex

By Burndy

Catalog # [YAV26L2TC38FX](#)

2/0 Flex G,H,I,K,M,DLO, 2/0 AWG, CU, 2 Hole, 3/8 Stud, 1 IN Spacing, Standard Barrel, Inspection Window

Features

- Electro-tin plated unless otherwise specified to reduce galvanic corrosion (bimetallic) and resist corrosive elements
- Connectors are clearly marked with stamping and barrel color coding
- For applications greater than 2000 Volts consult cable manufacturer for voltage stress relief instructions

Application

Wire Termination

Specifications

Certification - UL Recognized	No
Buy American Compliant	No
Certification - cULus	No
EU RoHS Indicator	Yes
Industry Standard(s)	UL 486A-486B
Certification - ETL	No
Standards - RoHS Compliance Status	CM
UL Listed	Yes
Certification - CSA Approved	Yes

Conductor

Conductor - Material	COPPER
Wire Size	2/0 AWG
Conductor - Copper Flex K Size Range	2/0 AWG
Conductor - Copper Flex K Size	"2/0 AWG"
Conductor - Copper Flex M Size Range	2/0 AWG
Conductor - Copper Flex M Size	"2/0 AWG"
Conductor - Copper Str Size	"2/0 AWG"
Conductor - Copper Flex I Size Range	2/0 AWG
Conductor - Copper Flex G Size	"2/0 AWG"
Conductor - Copper DLO Size Range	2/0 AWG
Conductor - Copper Str Compact Size	"2/0 AWG"
Conductor - Copper DLO Size	2/0 AWG
Conductor Size	2/0 AWG
Conductor - Copper Flex H Size	"2/0 AWG"



Conductor - Copper Flex G Size Range	2/0 AWG
Conductor - Copper Str Navy Size Range	125 (61) Navy
Conductor - Copper Str Navy Size	125
Conductor - Copper Solid Size Range	2/0 AWG
Conductor - Copper Solid Size	2/0 AWG
Conductor - CopperWeld Str Size Range	2/0 WELD
Conductor - CopperWeld Str Size	2/0 WELD
Conductor Type	CODE/FLEX
Conductor - Copper Str Size Range	2/0 AWG
Conductor - Copper Flex H Size Range	2/0 AWG
Conductor - Copper Flex I Size	"2/0 AWG"

Configuration

Physical Attribute - Number of Holes	2
Number of Pad Holes	2
Connector Type	STANDARD BARREL

Current

Voltage Rating	35 kV
Voltage - Maximum	35000

Dimensions

Dimension - Pad Width inch	0.93 in
Package Height	0.000 in
Dimension - Hole Size fraction	3/8
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall mm	79 mm
Dimension - Outside Diameter inch	0.63 in
Dimension - Hole Size mm	10.4 mm
Dimension - Hole Size inch	0.41
Dimension - Strip Length inch	13/16 in
Dimension - Stud Size fraction	3/8

Dimension - Bolt Hole Size inch	0.41 in	Sub Brand	HYLUG
Dimension - Bolt Size fraction	3/8	UPC	781810021767
Physical Attribute - Tongue Angle	Straight	Type	Standard Barrel, Tin Plated
Dimension - B Length fraction	13/16 in	Material	Copper
Dimension - Z inch	0.43 in	Plating Type	Tin
Dimension - B Length inch	0.81 in	Finish Type	Tin-Plated
Dimension - N inch	0.41 in	UPC 12 Digit	781810021767
Dimension - Bolt Size inch	0.38	UPC 14 Digit GTIN	00781810021767
Dimension - Length Overall inch	3.12 in		
General		Logistics	
Trade Name	HYLUG™	Minimum Pack Quantity	1
Die Index	13	Pallet Quantity	18500
Feature - Barrel Type	Standard	Carton Quantity	100
Feature - Barrel Style	- Chamfered - Skived	Operational	
Plated	Y	Temperature Rating	194
Color Code	Black	Product Assets	
Physical Attribute - Tongue Type	Standard	Catalog [English]	
		Installation Manual [English]	
		Installation Manual [English]	

