



## YAV26L3NK, Compression Terminal, 2/0 AWG, 1-Hole, 1/2" Stud, Standard Barrel, Nickel Plated

By Burndy

Catalog # [YAV26L3NK](#)

Copper Compression Terminal



### Features

- Seamless, heavy duty uninsulated compression terminal provides a strong connector for demanding applications requiring high reliability
- Suitable for use on Type AN aircraft cable, extra flexible conductors and commercial (code) conductors

### Application

Wire Termination

### Specifications

|                               |              |
|-------------------------------|--------------|
| Certification - UL Recognized | No           |
| Certification - cULus         | No           |
| Industry Standard(s)          | UL 486A-486B |
| Certification - ETL           | No           |
| Standards - RoHS Compliance   | CM           |
| Status                        |              |
| UL Listed                     | Yes          |
| Certification - CSA Approved  | Yes          |

### Conductor

|                                            |         |
|--------------------------------------------|---------|
| Conductor - Material                       | COPPER  |
| Conductor - Copper Str Size                | 2/0 AWG |
| Conductor Size                             | 2/0 AWG |
| Conductor - Copper Str Aircraft Size Range | AN-2/0  |
| Conductor - Copper Str Aircraft Size       | AN-2/0  |
| Conductor Type                             | CODE    |

### Configuration

|                                      |                 |
|--------------------------------------|-----------------|
| Physical Attribute - Number of Holes | 1               |
| Number of Pad Holes                  | 1               |
| Connector Type                       | STANDARD BARREL |

### Current

|                   |       |
|-------------------|-------|
| Voltage Rating    | 35 kV |
| Voltage - Maximum | 35000 |

### Dimensions

|                                |          |
|--------------------------------|----------|
| Dimension - Pad Width inch     | 0.93 in  |
| Package Height                 | 0.000 in |
| Dimension - Hole Size fraction | 1/2      |

|                                   |           |
|-----------------------------------|-----------|
| Package Weight                    | 0.000 lb. |
| Package Length                    | 0.000 in  |
| Package Width                     | 0.000 in  |
| Dimension - L Length Overall mm   | 59 mm     |
| Dimension - Hole Size mm          | 13.5 mm   |
| Dimension - Hole Size inch        | 0.53      |
| Dimension - Strip Length inch     | 13/16 in  |
| Dimension - Stud Size fraction    | 1/2       |
| Dimension - Bolt Hole Size inch   | 0.56 in   |
| Dimension - Bolt Size fraction    | 1/2       |
| Physical Attribute - Tongue Angle | Straight  |
| Dimension - B Length fraction     | 3/4 in    |
| Dimension - Z inch                | 0.48 in   |
| Dimension - B Length inch         | 0.78 in   |
| Dimension - N inch                | 0.47 in   |
| Dimension - Bolt Size inch        | 0.5       |
| Dimension - Length Overall inch   | 2.32 in   |

### General

|                                  |                                                                          |
|----------------------------------|--------------------------------------------------------------------------|
| Trade Name                       | HYLUG™                                                                   |
| Die Index                        | 13                                                                       |
| Feature - Barrel Type            | Standard                                                                 |
| Feature - Barrel Style           | <ul style="list-style-type: none"><li>Chamfered</li><li>Skived</li></ul> |
| Plated                           | Y                                                                        |
| Physical Attribute - Tongue Type | Ring                                                                     |
| UPC                              | 781810069707                                                             |
| Type                             | Standard Barrel, Nickel Plated                                           |
| Material                         | Copper                                                                   |
| Plating Type                     | Nickel                                                                   |
| Finish Type                      | Nickel Plated                                                            |
| UPC 12 Digit                     | 781810069707                                                             |
| UPC 14 Digit GTIN                | 00781810069707                                                           |

### Logistics

|                       |       |
|-----------------------|-------|
| Minimum Pack Quantity | 100   |
| Pallet Quantity       | 29000 |
| Carton Quantity       | 100   |

### Operational

|                    |     |
|--------------------|-----|
| Temperature Rating | 194 |
|--------------------|-----|



A Hubbell brand