



YAV26LNT12FX, Compression Terminal, 2/0 Flex G,H,I,K,M,DLO, 2/0 AWG, CU, 1 Hole, 1/2" Stud, Narrow Tongue

By Burndy
Catalog # [YAV26LNT12FX](#)

2/0 Flex G,H,I,K,M,DLO, 2/0 AWG, CU, 1 Hole, 1/2 Stud, Standard Barrel, Inspection WIndow, Narrow Tongue

Features

- Electro-tin plated unless otherwise specified to reduce galvanic corrosion (bimetallic) and resist corrosive elements
- Connectors are clearly marked with stamping and barrel color coding
- For applications greater than 2000 Volts consult cable manufacturer for voltage stress relief instructions

Application

Wire Termination

Specifications

Standards - RoHS Compliance	CM
Status	
Industry Standard(s)	UL 486A-486B
UL Listed	Yes
Certification - CSA Approved	Yes

Conductor

Conductor - Copper Flex G Size	"2/0 AWG"
Conductor - Copper DLO Size	2/0 AWG
Range	
Conductor - Copper Str	"2/0 AWG"
Compact Size	
Conductor - Copper DLO Size	2/0 AWG
Conductor Size	2/0 AWG
Conductor - Copper Flex H Size	"2/0 AWG"
Conductor - Copper Str Navy	125 (61) Navy
Size Range	
Conductor - Copper Flex G Size	2/0 AWG
Range	
Conductor - Copper Str Navy	125
Size	
Conductor - Material	COPPER
Wire Size	2/0 AWG
Conductor - Copper Flex K Size	2/0 AWG
Range	
Conductor - Copper Flex K Size	"2/0 AWG"
Conductor - Copper Flex M Size	"2/0 AWG"
Conductor Type	CODE/FLEX
Conductor - Copper Str Size	2/0 AWG
Range	
Conductor - Copper Str Size	"2/0 AWG"



Conductor - Copper Flex H Size	2/0 AWG
Range	
Conductor - Copper Flex I Size	"2/0 AWG"
Conductor - Copper Flex I Size	2/0 AWG
Range	

Configuration

Physical Attribute - Number of Holes	1
Number of Pad Holes	1
Connector Type	STANDARD BARREL

Current

Voltage Rating	35 kV
Voltage - Maximum	35000

Dimensions

Dimension - Pad Width inch	0.87 in
Package Height	0.000 in
Dimension - Hole Size fraction	1/2
Dimension - Bolt Size fraction	1/2
Physical Attribute - Tongue Angle	Straight
Dimension - B Length fraction	13/16 in
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall	60 mm
mm	
Dimension - B Length inch	0.81 in
Dimension - Outside Diameter	0.63 in
inch	
Dimension - N inch	0.53 in
Dimension - Inside Diameter	0.51 in
inch	
Dimension - Hole Size mm	13.5 mm
Dimension - Bolt Size inch	0.5
Dimension - Hole Size inch	0.53
Dimension - Length Overall	2.36 in
inch	
Dimension - Strip Length inch	13/16
Dimension - Stud Size inch	1/2
Dimension - Stud Size fraction	1/2

General

Feature - Barrel Type	Standard	UPC 14 Digit GTIN	00781810250341
Feature - Barrel Style	Chamfered		
Plated	Y	Logistics	
Color Code	Black	Carton Quantity	10
Trade Name	HYLUG™		
Die Index	13	Product Assets	
UPC	781810250341	Catalog [English]	
Material	Copper	Installation Manual [English]	
Plating Type	Tin - Electro Plated	Installation Manual [English]	
Finish Type	Tin-Plated		



A Hubbell brand