



YAV26LNT516FX, Compression Terminal, 2/0 Flex G,H,I,K,M,DLO, 2/0 AWG, CU, 1 Hole, 5/16" Stud, Narrow Tongue

By Burndy

Catalog # [YAV26LNT516FX](#)

2/0 Flex G,H,I,K,M,DLO, 2/0 AWG, CU, 1 Hole, 5/16 Stud, Standard
Barrel, Inspection WIndow, Narrow Tongue

Features

- Electro-tin plated unless otherwise specified to reduce galvanic corrosion (bimetallic) and resist corrosive elements
- Connectors are clearly marked with stamping and barrel color coding
- For applications greater than 2000 Volts consult cable manufacturer for voltage stress relief instructions

Application

Wire Termination

Specifications

Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL 486A-486B
Certification - ETL	No
Standards - RoHS Compliance	CM
Status	
UL Listed	Yes
Certification - CSA Approved	Yes

Conductor

Conductor - Material	COPPER
Wire Size	2/0 AWG
Conductor - Copper Flex K Size	2/0 AWG
Range	
Conductor - Copper Flex K Size	"2/0 AWG"
Conductor - Copper Flex M Size	"2/0 AWG"
Conductor - Copper Str Size	"2/0 AWG"
Conductor - Copper Flex I Size	2/0 AWG
Range	
Conductor - Copper Flex G Size	"2/0 AWG"
Conductor - Copper DLO Size	2/0 AWG
Range	
Conductor - Copper Str	"2/0 AWG"
Compact Size	
Conductor - Copper DLO Size	2/0 AWG
Conductor Size	2/0 AWG
Conductor - Copper Flex H Size	"2/0 AWG"
Conductor - Copper Flex G Size	2/0 AWG
Range	
Conductor - Copper Str Navy	125 (61) Navy
Size Range	



Conductor - Copper Str Navy	125
Size	
Conductor Type	CODE/FLEX
Conductor - Copper Str Size	2/0 AWG
Range	
Conductor - Copper Flex H Size	2/0 AWG
Range	
Conductor - Copper Flex I Size	"2/0 AWG"

Configuration

Physical Attribute - Number of	1
Holes	
Number of Pad Holes	1
Connector Type	STANDARD BARREL

Current

Voltage Rating	35 kV
Voltage - Maximum	35000

Dimensions

Dimension - Pad Width inch	0.87 in
Package Height	0.000 in
Dimension - Hole Size fraction	5/16
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall	50 mm
mm	
Dimension - Outside Diameter	0.63 in
inch	
Dimension - Hole Size mm	10 mm
Dimension - Hole Size inch	0.38
Dimension - Strip Length inch	13/16
Dimension - Stud Size inch	5/16
Dimension - Stud Size fraction	5/16
Dimension - Bolt Hole Size inch	0.33 in
Dimension - Bolt Size fraction	5/16
Physical Attribute - Tongue	Straight
Angle	
Dimension - B Length fraction	13/16 in
Dimension - Z inch	0.36 in
Dimension - B Length inch	0.81 in
Dimension - N inch	0.34 in
Dimension - Bolt Size inch	0.3125

Dimension - Length Overall inch	1.98 in	Plating Type	Tin
		Finish Type	Tin-Plated
		UPC 14 Digit GTIN	00781810098585
General		Logistics	
Trade Name	HYLUG™	Minimum Pack Quantity	10
Die Index	13	Carton Quantity	10
Feature - Barrel Type	Standard		
Feature - Barrel Style	Chamfered		
Plated	Y		
Color Code	Black		
UPC	781810098585		
Material	Copper		
		Product Assets	
		Catalog [English]	
		Installation Manual [English]	
		Installation Manual [English]	



A Hubbell brand