



YAV26LTC10FX45, Compression Terminal, 2/0 Flex G,H,I,K,M, DLO, 2/0 AWG, Cu, 1-Hole, #10 Stud, Standard Barrel, 45 Degree

By Burndy
Catalog # [YAV26LTC10FX45](#)

2/0 Flex G,H,I,K,M,DLO, 2/0 AWG, CU, 1 Hole, #10 Stud, Standard Barrel, Inspection Window, 45 Degree

Features

- Electro-tin plated unless otherwise specified to reduce galvanic corrosion (bimetallic) and resist corrosive elements
- Connectors are clearly marked with stamping and barrel color coding
- For applications greater than 2000 Volts consult cable manufacturer for voltage stress relief instructions

Application

Wire Termination

Specifications

Standards - RoHS Compliance Status	CM
Industry Standard(s)	UL 486A-486B

Conductor

Conductor - Copper Flex G Size	"2/0 AWG"
Conductor - Copper DLO Size Range	2/0 AWG
Conductor - Copper Str Compact Size	"2/0 AWG"
Conductor - Copper DLO Size	2/0 AWG
Conductor Size	2/0 AWG
Conductor - Copper Flex H Size	"2/0 AWG"
Conductor - Copper Flex G Size Range	2/0 AWG
Conductor - Copper Str Navy Size Range	125 Navy
Conductor - Copper Str Navy Size	125
Conductor - Material	COPPER
Wire Size	2/0 AWG
Conductor - Copper Flex K Size Range	2/0 AWG
Conductor - Copper Flex K Size	"2/0 AWG"
Conductor - CopperWeld Str Size	• 2/0 F AWG • 2/0 G AWG • 2/0 J AWG • 2/0 K AWG • 2/0 V AWG
Conductor - Copper Flex M Size	"2/0 AWG"
Conductor Type	CODE/FLEX



Conductor - Copper Str Size Range	2/0 AWG
Conductor - Copper Str Size	"2/0 AWG"
Conductor - Copper Flex H Size Range	2/0 AWG
Conductor - Copper Flex I Size	"2/0 AWG"
Conductor - Copper Flex I Size Range	2/0 AWG

Configuration

Physical Attribute - Number of Holes	1
Number of Pad Holes	1
Connector Type	STANDARD BARREL

Current

Voltage Rating	35 kV
Voltage - Maximum	35000

Dimensions

Dimension - Pad Width inch	0.93 in
Dimension - Bolt Hole Size inch	0.21 in
Dimension - Hole Size fraction	#10
Dimension - Bolt Size fraction	#8-#10
Physical Attribute - Tongue Angle	45 Degree
Angle - Pad	45 °
Dimension - Z inch	0.27 in
Dimension - L Length Overall mm	44 mm
Dimension - B Length inch	0.81 in
Dimension - Outside Diameter inch	0.63 in
Dimension - N inch	0.25 in
Dimension - Hole Size mm	5.3 mm
Dimension - Bolt Size inch	0.21
Dimension - Hole Size inch	0.21
Dimension - Length Overall inch	1.73 in
Dimension - Strip Length inch	13/16
Dimension - Stud Size fraction	#10

General

Feature - Barrel Type	Standard
-----------------------	----------

Feature - Barrel Style	Chamfered	Finish Type	Tin-Plated
Plated	Yes	UPC 12 Digit	781810322635
Color Code	Black	UPC 14 Digit GTIN	00781810322635
Trade Name	HYLUG™	Logistics	
Die Index	13	Minimum Pack Quantity	1
UPC	781810322635	Product Assets	
Type	Long Barrel, Tin Plated	Catalog [English]	
Material	Copper		
Plating Type	Tin		



A Hubbell brand