



YAV26LTC10FX90, Compression Terminal,
2/0 Flex G,H,I,K,M, DLO, 2/0 AWG, Cu, 1-
Hole, #10 Stud, Standard Barrel, 90 Degree

By Burndy
Catalog # [YAV26LTC10FX90](#)

2/0 Flex G,H,I,K,M,DLO, 2/0 AWG, CU, 1 Hole, #10 Stud, Standard
Barrel, Inspection Window, 90 Degree

Features

- Electro-tin plated unless otherwise specified to reduce galvanic corrosion (bimetallic) and resist corrosive elements
- Connectors are clearly marked with stamping and barrel color coding
- For applications greater than 2000 Volts consult cable manufacturer for voltage stress relief instructions

Application

Wire Termination

Specifications

Standards - RoHS Compliance Status	CM
Industry Standard(s)	UL 486A-486B

Conductor

Conductor - Copper Flex G Size	"2/0 AWG"
Conductor - Copper DLO Size Range	2/0 AWG
Conductor - Copper Str Compact Size	"2/0 AWG"
Conductor - Copper DLO Size	2/0 AWG
Conductor Size	2/0 AWG
Conductor - Copper Flex H Size	"2/0 AWG"
Conductor - Copper Flex G Size Range	2/0 AWG
Conductor - Copper Str Navy Size Range	125 Navy
Conductor - Copper Str Navy Size	125
Conductor - Material	COPPER
Wire Size	2/0 AWG
Conductor - Copper Flex K Size Range	2/0 AWG
Conductor - Copper Flex K Size	"2/0 AWG"
Conductor - CopperWeld Str Size	• 2/0 F AWG • 2/0 G AWG • 2/0 J AWG • 2/0 K AWG • 2/0 V AWG
Conductor - Copper Flex M Size	"2/0 AWG"
Conductor Type	CODE/FLEX



Conductor - Copper Str Size Range	2/0 AWG
Conductor - Copper Str Size	"2/0 AWG"
Conductor - Copper Flex H Size Range	2/0 AWG
Conductor - Copper Flex I Size	"2/0 AWG"
Conductor - Copper Flex I Size Range	2/0 AWG

Configuration

Physical Attribute - Number of Holes	1
Number of Pad Holes	1
Connector Type	STANDARD BARREL

Current

Voltage Rating	35 kV
Voltage - Maximum	35000

Dimensions

Dimension - Pad Width inch	0.93 in
Dimension - Bolt Hole Size inch	0.21 in
Dimension - Hole Size fraction	#10
Dimension - Bolt Size fraction	#8-#10
Physical Attribute - Tongue Angle	90 Degree
Angle - Pad	90 °
Dimension - Z inch	0.27 in
Dimension - L Length Overall mm	24 mm
Dimension - B Length inch	0.81 in
Dimension - Outside Diameter inch	0.63 in
Dimension - N inch	0.25 in
Dimension - Hole Size mm	5.3 mm
Dimension - Bolt Size inch	0.21
Dimension - Hole Size inch	0.21
Dimension - Length Overall inch	0.94 in
Dimension - Strip Length inch	13/16
Dimension - Stud Size fraction	#10

General

Feature - Barrel Type	Standard
-----------------------	----------

Feature - Barrel Style	Chamfered	Finish Type	Tin-Plated
Plated	Yes	UPC 12 Digit	781810322642
Color Code	Black	UPC 14 Digit GTIN	00781810322642
Trade Name	HYLUG™		
Die Index	13	Logistics	
UPC	781810322642	Minimum Pack Quantity	1
Type	Long Barrel, Tin Plated		
Material	Copper	Product Assets	
Plating Type	Tin	Catalog [English]	



A Hubbell brand