



YAV26LTC12FX, Cu Compression, 1-Hole, 1/2" Stud, Standard Barrel, 2/0 Flex

By Burndy

Catalog # [YAV26LTC12FX](#)

2/0 Flex G,H,I,K,M,DLO, 2/0 AWG, CU, 1 Hole, 1/2 Stud, Standard Barrel, Inspection Window

Features

- Electro-tin plated unless otherwise specified to reduce galvanic corrosion (bimetallic) and resist corrosive elements
- Connectors are clearly marked with stamping and barrel color coding
- For applications greater than 2000 Volts consult cable manufacturer for voltage stress relief instructions

Application

Wire Termination

Specifications

Certification - UL Recognized	No
Buy American Compliant	Contact Manufacturer
Certification - cULus	No
EU RoHS Indicator	Yes
Buy America(n) Qualified	Contact Manufacturer
Industry Standard(s)	UL 486A-486B
Certification - ETL	No
Standards - RoHS Compliance Status	CM
UL Listed	Yes
Certification - CSA Approved	Yes

Conductor

Conductor - Material	COPPER
Wire Size	2/0 AWG
Conductor - Copper Flex K Size Range	2/0 AWG
Conductor - Copper Flex K Size	"2/0 AWG"
Conductor - Copper Flex M Size	"2/0 AWG"
Conductor - Copper Str Size	"2/0 AWG"
Conductor - Copper Flex I Size Range	2/0 AWG
Conductor - Copper Flex G Size	"2/0 AWG"
Conductor - Copper DLO Size Range	2/0 AWG
Conductor - Copper Str Compact Size	"2/0 AWG"
Conductor - Copper DLO Size	2/0 AWG
Conductor Size	2/0 AWG
Conductor - Copper Flex H Size	"2/0 AWG"
Conductor - Copper Flex G Size Range	2/0 AWG



Conductor - Copper Str Navy Size Range	125 (61) Navy
Conductor - Copper Str Navy Size	125
Conductor - CopperWeld Str Size	• 2/0 F AWG • 2/0 G AWG • 2/0 J AWG • 2/0 K AWG • 2/0 V AWG

Conductor Type	CODE/FLEX
Conductor - Copper Str Size Range	2/0 AWG
Conductor - Copper Flex H Size Range	2/0 AWG
Conductor - Copper Flex I Size	"2/0 AWG"

Configuration

Physical Attribute - Number of Holes	1
Number of Pad Holes	1
Connector Type	STANDARD BARREL

Current

Voltage Rating	35 kV
Voltage - Maximum	35000

Dimensions

Dimension - Pad Width inch	0.93 in
Package Height	0.000 in
Dimension - Height mm	0 mm
Dimension - Hole Size fraction	1/2
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall mm	60 mm
Dimension - Outside Diameter inch	0.63 in
Dimension - Hole Size mm	13.5 mm
Dimension - Hole Size inch	0.53
Dimension - Strip Length inch	13/16
Dimension - Stud Size inch	1/2
Dimension - Stud Size fraction	1/2
Dimension - Bolt Hole Size inch	0.53 in
Dimension - Bolt Size fraction	1/2

Physical Attribute - Tongue Angle	Straight	Sub Brand	HYLUG
Dimension - Z inch	0.55 in	UPC	781810021972
Dimension - B Length inch	0.81 in	Type	Standard Barrel, Tin Plated
Dimension - N inch	0.53 in	Material	Copper
Dimension - Bolt Size inch	0.5	Plating Type	Tin
Dimension - Length Overall inch	2.36 in	Finish Type	Tin-Plated
		UPC 12 Digit	781810021972
		UPC 14 Digit GTIN	00781810021972
General		Logistics	
Trade Name	HYLUG™	Minimum Pack Quantity	1
Die Index	13	Pallet Quantity	23200
Feature - Barrel Type	Standard	Carton Quantity	100
Feature - Barrel Style	Chamfered		
Plated	Yes	Product Assets	
Color Code	Black	Catalog [English]	
Physical Attribute - Tongue Type	Standard	Installation Manual [English]	
		Installation Manual [English]	



A Hubbell brand